POSITAL
FRABA

## IXARC Absolute Rotary Encoder

## OCD-P1A1G-0016-C10S-2RW



| **Interface** | |
|---|---|
| Interface | Bit Parallel preset |
| Manual Functions | Preset + complement via cable or connector |
| Interface Cycle Time | 150 µs |

| **Outputs** | |
|---|---|
| Output Driver | Push-Pull |

| **Electrical Data** | |
|---|---|
| Supply Voltage | 10 – 30 VDC |
| Current Consumption | ≤ 400 mA @ 10 V DC, ≤ 180 mA @ 24 V DC |
| Power Consumption | ≤ 1.5 W |
| Start-Up Time | < 250 ms |
| Settling Time | 80 ms |
| Reverse Polarity Protection | Yes |
| Short Circuit Protection | Yes |
| EMC: Emitted Interference | DIN EN 61000-6-4 |
| EMC: Noise Immunity | DIN EN 61000-6-2 |
| MTTF | 22.3 years @ 40 °C |

| **Sensor** | |
|---|---|
| Technology | Optical |

| | |
|---|---|
| Resolution Singleturn | 16 bit |
| Accuracy (INL) | ±0.0220° (14 – 16 bit), ±0.0439° (≤13 bit) |
| Sense Signal (Default) | Clockwise shaft movement (front view on shaft) |
| Code | Gray |

**Environmental Specifications**

| | |
|---|---|
| Protection Class (Shaft) | IP66/IP67 |
| Protection Class (Housing) | IP66/IP67 |
| Operating Temperature | -30 °C fixed (-22 °F), -5 °C flexible (+23 °F) - +70 °C (+158 °F) |
| Humidity | 98% RH, no condensation |

**Mechanical Data**

| | |
|---|---|
| Housing Material | Steel |
| Housing Coating | Wet coating (RAL 9006 White Aluminium) + Cathodic corrosion protection (>720 h salt spay resistance) |
| Flange Type | Clamp, ø 58 mm (C) |
| Flange Material | Aluminum |
| Shaft Type | Solid, Single Flat, Length = 20 mm |
| Shaft Diameter | ø 10 mm (0.39") |
| Shaft Material | Stainless Steel V2A (1.4305, 303) |
| Max. Shaft Load | Axial 40 N, Radial 110 N |
| Minimum Mechanical Lifetime (10^8 revolutions with Fa/Fr) | 430 (20 N / 40 N), 150 (40 N / 60 N), 100 (40 N / 80 N), 55 (40 N / 110 N) |
| Rotor Inertia | ≤ 30 gcm² [≤ 0.17 oz-in²] |
| Friction Torque | ≤ 5 Ncm @ 20 °C, (7.1 oz-in @ 68 °F) |
| Max. Permissible Mechanical Speed | ≤ 3000 1/min |
| Shock Resistance | ≤ 100 g (half sine 6 ms, EN 60068-2-27) |
| Permanent Shock Resistance | ≤ 10 g (half sine 16 ms, EN 60068-2-29) |
| Vibration Resistance | ≤ 10 g (10 Hz – 1000 Hz, EN 60068-2-6) |
| Length | 52,7 mm (2.07") |
| Weight | 295 g (0.65 lb) |

**Electrical Connection**


| | |
|---|---|
| Connection Orientation | Radial |
| Cable Length | 2 m [79"] |
| Wire Cross Section | 0.14 mm² / AWG 26 |

| | |
|---|---|
| Material / Type | PVC |
| Cable Diameter | 9.3 mm (0.37 in) |
| Minimum Bend Radius | 150 mm (6 in) |

**Certification**

| | |
|---|---|
| Approval | CE + cULus listed, Industrial Control Equipment |
| Product Life Cycle | Established |

**Connection Plan**




2D Drawing

**Accessories**

Clamp Disc w/ Eccentric Hole-4pcs
Clamp Disc w/ Centred Hole-4pcs

Coupling Disc Type-10-12

Coupling Bellow Type-10-10
Coupling Bellow Type-06-10
Coupling Bellow Type-08-10
Coupling Bellow Type-10-12
Coupling Bellow Type-10-(1/4")
Coupling Bellow Type-10-(3/8")
Coupling Jaw Type-06-10
Coupling Jaw Type-08-10
Coupling Jaw Type-10-12
Coupling Jaw Type-10-(1/4")
Coupling Jaw Type-10-(3/8")
Coupling Jaw Type-10-10
Coupling Disc Type-06-10
Coupling Disc Type-10-10
More

Mounting Bracket for Clamping Flange w/ fixtures
L Mounting Bracket w/ screws
Mounting Bracket Spring Loaded f. Clamping Flange

**Contact**

POSITAL
Contact Us

The picture and drawing are for general presentation purposes only. Please refer to the "Download" section for detailed technical drawings. All dimension in [inch] mm. © FRABA B.V., All rights reserved. We do not assume responsibility for technical inaccuracies or omissions. Specifications are subject to change without notice.