



### IXARC Absolute Rotary Encoder

OCD-S101G-1416-SB90-PRL



#### Interface

|                      |                                            |
|----------------------|--------------------------------------------|
| Interface            | SSI with Preset                            |
| Manual Functions     | Preset + complement via cable or connector |
| Interface Cycle Time | $\geq 25 \mu\text{s}$                      |

#### Outputs

|               |       |
|---------------|-------|
| Output Driver | RS422 |
|---------------|-------|

#### Electrical Data

|                             |                         |
|-----------------------------|-------------------------|
| Supply Voltage              | 4.5 – 30 VDC            |
| Power Consumption           | $\leq 1.5 \text{ W}$    |
| Start-Up Time               | $< 250 \text{ ms}$      |
| Clock Input                 | RS 422, via Optocoupler |
| Clock Frequency             | 100 kHz – 2 MHz         |
| Reverse Polarity Protection | Yes                     |
| Short Circuit Protection    | Yes                     |
| EMC: Emitted Interference   | DIN EN 61000-6-4        |
| EMC: Noise Immunity         | DIN EN 61000-6-2        |
| MTTF                        | 16.2 years @ 40 °C      |

#### Sensor

|            |         |
|------------|---------|
| Technology | Optical |
|------------|---------|

Data Sheet

Printed at 27-09-2017 16:09

# POSITAL

## FRABA



|                        |                                                                       |
|------------------------|-----------------------------------------------------------------------|
| Resolution Singleturn  | 16 bit                                                                |
| Resolution Multiturn   | 14 bit                                                                |
| Multiturn Technology   | Mechanical Gearing (no Battery)                                       |
| Accuracy (INL)         | $\pm 0.0220^\circ$ (14 - 16 bit), $\pm 0.0439^\circ$ ( $\leq 13$ bit) |
| Sense Signal (Default) | Clockwise shaft movement (front view on shaft)                        |
| Code                   | Gray                                                                  |

### Environmental Specifications

|                            |                                    |
|----------------------------|------------------------------------|
| Protection Class (Shaft)   | IP65                               |
| Protection Class (Housing) | IP65                               |
| Operating Temperature      | -40 °C (-40 °F) - +85 °C (+185 °F) |
| Humidity                   | 98% RH, no condensation            |

### Mechanical Data

|                                                                 |                                                                                                       |
|-----------------------------------------------------------------|-------------------------------------------------------------------------------------------------------|
| Housing Material                                                | Steel                                                                                                 |
| Housing Coating                                                 | Wet coating (RAL 9006 White Aluminium) + Cathodic corrosion protection (>720 h salt spray resistance) |
| Flange Type                                                     | Synchro, $\varnothing$ 58 mm (S)                                                                      |
| Flange Material                                                 | Aluminum                                                                                              |
| Shaft Type                                                      | Solid, Single Flat, Length = 20 mm                                                                    |
| Shaft Diameter                                                  | $\varnothing$ 10 mm (0.39")                                                                           |
| Shaft Material                                                  | Stainless Steel V2A (1.4305, 303)                                                                     |
| Max. Shaft Load                                                 | Axial 40 N, Radial 110 N                                                                              |
| Minimum Mechanical Lifetime<br>( $10^8$ revolutions with Fa/Fr) | 420 (20 N / 40 N), 145 (40 N / 60 N), 100 (40 N / 80 N), 55 (40 N / 110 N)                            |
| Rotor Inertia                                                   | $\leq 30 \text{ gcm}^2$ [ $\leq 0.17 \text{ oz-in}^2$ ]                                               |
| Friction Torque                                                 | $\leq 3 \text{ Ncm}$ @ 20 °C (4.2 oz-in @ 68 °F)                                                      |
| Max. Permissible Mechanical Speed                               | $\leq 12000 \text{ 1/min}$                                                                            |
| Shock Resistance                                                | $\leq 100 \text{ g}$ (half sine 6 ms, EN 60068-2-27)                                                  |
| Permanent Shock Resistance                                      | $\leq 10 \text{ g}$ (half sine 16 ms, EN 60068-2-29)                                                  |
| Vibration Resistance                                            | $\leq 10 \text{ g}$ (10 Hz - 1000 Hz, EN 60068-2-6)                                                   |
| Length                                                          | 56,7 mm (2.23")                                                                                       |
| Weight                                                          | 280 g (0.62 lb)                                                                                       |

### Electrical Connection

|                        |                               |
|------------------------|-------------------------------|
| Connection Orientation | Radial                        |
| Connector              | M23, Male, 12 pin, CCW / left |

Data Sheet

Printed at 27-09-2017 16:09


# POSITAL

## FRABA



### Certification


|                    |                                                 |
|--------------------|-------------------------------------------------|
| Approval           | CE + cULus listed, Industrial Control Equipment |
| Product Life Cycle | Established                                     |



### Connection Plan

| SIGNAL        | PIN NUMBER |
|---------------|------------|
| Power Supply  | 11         |
| GND           | 12         |
| Data+         | 3          |
| Data-         | 4          |
| Clock+        | 2          |
| Clock-        | 1          |
| Preset        | 9          |
| DIR           | 8          |
| Not Connected | 5          |
| Not Connected | 6          |
| Not Connected | 7          |
| Not Connected | 10         |

Connector-View on Encoder



### [2D Drawing](#)

### Accessories

#### Connectors & Cables

10m PVC Cable, 12pin, Clockwise, f  
15m PVC Cable, 12pin, Clockwise, f  
1m PVC Cable, 12pin, Clockwise, f  
20m PVC Cable, 12pin, Clockwise, f  
5m PVC Cable, 12pin, Clockwise, f  
30m PVC Cable, 12pin, Clockwise, f  
2m PVC Cable, 12pin, Clockwise, f  
M23, 12pin Clockwise, Female  
More

Clamp Disc w/ Eccentric Hole-4pcs  
Clamp Disc w/ Centred Hole-4pcs

Coupling Disc Type-10-12

Data Sheet

Printed at 27-09-2017 16:09



Coupling Bellow Type-10-10  
Coupling Bellow Type-06-10  
Coupling Bellow Type-08-10  
Coupling Bellow Type-10-12  
Coupling Bellow Type-10-(1/4")  
Coupling Bellow Type-10-(3/8")  
Coupling Jaw Type-08-10  
Coupling Jaw Type-10-12  
Coupling Jaw Type-10-(1/4")  
Coupling Jaw Type-10-(3/8")  
Coupling Jaw Type-10-10  
Coupling Disc Type-06-10  
Coupling Disc Type-10-10  
More

Mounting Bracket for Synchro Flange w/ fixtures

### Contact



POSITAL  
Contact Us

The picture and drawing are for general presentation purposes only. Please refer to the "Download" section for detailed technical drawings. All dimension in [inch] mm. © FRABA B.V., All rights reserved. We do not assume responsibility for technical inaccuracies or omissions. Specifications are subject to change without notice.