



### IXARC Absolute Rotary Encoder

OCD-S6C1B-0016-CA30-PRP



#### Interface

|                             |                                            |
|-----------------------------|--------------------------------------------|
| Interface                   | SSI with Preset + Incremental Push Pull    |
| Optional Incremental Pulses | 4096                                       |
| Manual Functions            | Preset + complement via cable or connector |
| Interface Cycle Time        | $\geq 25 \mu\text{s}$                      |

#### Outputs

|                         |                                     |
|-------------------------|-------------------------------------|
| Output Driver           | SSI (RS422) / Incr. (Push Pull)     |
| Output Incremental      | A, /A, B, /B, Z, /Z                 |
| Quadrature Phasing      | $90^\circ \pm 4.5^\circ$ electrical |
| Max. Frequency Response | 2 MHz                               |

#### Electrical Data

|                             |                         |
|-----------------------------|-------------------------|
| Supply Voltage              | 10 - 30 VDC             |
| Power Consumption           | $\leq 1.5 \text{ W}$    |
| Start-Up Time               | $< 250 \text{ ms}$      |
| Clock Input                 | RS 422, via Optocoupler |
| Clock Frequency             | 100 kHz - 2 MHz         |
| Reverse Polarity Protection | Yes                     |
| Short Circuit Protection    | Yes                     |
| EMC: Emitted Interference   | DIN EN 61000-6-4        |
| EMC: Noise Immunity         | DIN EN 61000-6-2        |

Data Sheet

Printed at 27-09-2017 20:09

# POSITAL

## FRABA



|      |                    |
|------|--------------------|
| MTTF | 16.2 years @ 40 °C |
|------|--------------------|

### Sensor

|                        |                                                                       |
|------------------------|-----------------------------------------------------------------------|
| Technology             | Optical                                                               |
| Resolution Singleturn  | 16 bit                                                                |
| Accuracy (INL)         | $\pm 0.0220^\circ$ (14 - 16 bit), $\pm 0.0439^\circ$ ( $\leq 13$ bit) |
| Sense Signal (Default) | Clockwise shaft movement (front view on shaft)                        |
| Code                   | Binary                                                                |
| Incremental Pulses     | 4096                                                                  |

### Environmental Specifications

|                            |                                    |
|----------------------------|------------------------------------|
| Protection Class (Shaft)   | IP65                               |
| Protection Class (Housing) | IP65                               |
| Operating Temperature      | -40 °C (-40 °F) - +85 °C (+185 °F) |
| Humidity                   | 98% RH, no condensation            |

### Mechanical Data

|                                                                 |                                                                                                       |
|-----------------------------------------------------------------|-------------------------------------------------------------------------------------------------------|
| Housing Material                                                | Steel                                                                                                 |
| Housing Coating                                                 | Wet coating (RAL 9006 White Aluminium) + Cathodic corrosion protection (>720 h salt spray resistance) |
| Flange Type                                                     | Clamp, $\varnothing$ 58 mm (C)                                                                        |
| Flange Material                                                 | Aluminum                                                                                              |
| Shaft Type                                                      | Solid, Single Flat, Length = 20 mm                                                                    |
| Shaft Diameter                                                  | $\varnothing$ 10 mm (0.39")                                                                           |
| Shaft Material                                                  | Stainless Steel V2A (1.4305, 303)                                                                     |
| Max. Shaft Load                                                 | Axial 40 N, Radial 110 N                                                                              |
| Minimum Mechanical Lifetime<br>( $10^8$ revolutions with Fa/Fr) | 430 (20 N / 40 N), 150 (40 N / 60 N), 100 (40 N / 80 N), 55 (40 N / 110 N)                            |
| Rotor Inertia                                                   | $\leq 30 \text{ gcm}^2$ [ $\leq 0.17 \text{ oz-in}^2$ ]                                               |
| Friction Torque                                                 | $\leq 3 \text{ Ncm}$ @ 20 °C (4.2 oz-in @ 68 °F)                                                      |
| Max. Permissible Mechanical Speed                               | $\leq 12000 \text{ 1/min}$                                                                            |
| Shock Resistance                                                | $\leq 100 \text{ g}$ (half sine 6 ms, EN 60068-2-27)                                                  |
| Permanent Shock Resistance                                      | $\leq 10 \text{ g}$ (half sine 16 ms, EN 60068-2-29)                                                  |
| Vibration Resistance                                            | $\leq 10 \text{ g}$ (10 Hz - 1000 Hz, EN 60068-2-6)                                                   |
| Length                                                          | 52,7 mm (2.07")                                                                                       |
| Weight                                                          | 285 g (0.63 lb)                                                                                       |

Data Sheet

Printed at 27-09-2017 20:09

# POSITAL

## FRABA



### Electrical Connection

|                        |                   |
|------------------------|-------------------|
| Connection Orientation | Radial            |
| Connector              | M23, Male, 16 pin |

### Certification

|                    |                                                 |
|--------------------|-------------------------------------------------|
| Approval           | CE + cULus listed, Industrial Control Equipment |
| Product Life Cycle | Established                                     |



### Connection Plan

| SIGNAL       | PIN NUMBER |
|--------------|------------|
| Power Supply | 11         |
| GND          | 12         |
| Data+        | 3          |
| Data-        | 4          |
| Clock+       | 2          |
| Clock-       | 1          |
| DIR          | 8          |
| Preset       | 9          |
| A            | 5          |
| /A           | 6          |
| B            | 7          |
| /B           | 10         |
| Z            | 13         |
| /Z           | 14         |
| Shielding    | Housing    |




### Connector-View on Encoder

### Pulse Diagram



### Rotation Clockwise (seen on shaft)



### 2D Drawing



### Accessories

Connectors & Cables

5m PVC Cable, 16pin, f

1m PVC Cable, 16pin, f

2m PVC Cable, 16pin, f

10m PVC Cable, 16pin, f

M23, 16pin, Female

More

Clamp Disc w/ Eccentric Hole-4pcs

Clamp Disc w/ Centred Hole-4pcs

Coupling Disc Type-10-12

Coupling Bellow Type-10-10

Coupling Bellow Type-06-10

Coupling Bellow Type-08-10

Coupling Bellow Type-10-12

Coupling Bellow Type-10-(1/4")

Coupling Bellow Type-10-(3/8")

Coupling Jaw Type-06-10

Coupling Jaw Type-08-10

Coupling Jaw Type-10-12

Coupling Jaw Type-10-(1/4")

Coupling Jaw Type-10-(3/8")

Coupling Jaw Type-10-10

Coupling Disc Type-06-10

Coupling Disc Type-10-10

More

Mounting Bracket for Clamping Flange w/ fixtures

L Mounting Bracket w/ screws

Mounting Bracket Spring Loaded f. Clamping Flange

### Contact

# POSITAL

---

## FRABA



POSITAL  
Contact Us

The picture and drawing are for general presentation purposes only. Please refer to the "Download" section for detailed technical drawings.  
All dimension in [inch] mm. © FRABA B.V., All rights reserved. We do not assume responsibility for technical inaccuracies or omissions.  
Specifications are subject to change without notice.