



# POSITAL

## FRABA

### IXARC Absolute Rotary Encoder

#### UCD-S101B-2012-L06S-PAL



#### Interface

|                         |                                                     |
|-------------------------|-----------------------------------------------------|
| Interface               | SSI with Preset                                     |
| Programming Functions   | Absolute: Resolution, Revolution, Code, Preset      |
| Manual Functions        | Preset + complement via cable or connector          |
| Interface Cycle Time    | $\geq 25 \mu\text{s}$                               |
| Number of Preset Cycles | 5,100,000                                           |
| SSI Format              | MMMMMMMMMMMMMMMMMMMMMMMMMMMMSSSSSSSSSSSSSS          |
| Video Manual            | <a href="#">▶ Watch a simple installation video</a> |

#### Outputs

|               |       |
|---------------|-------|
| Output Driver | RS422 |
|---------------|-------|

#### Electrical Data

|                             |                         |
|-----------------------------|-------------------------|
| Supply Voltage              | 4.5 – 30 VDC            |
| Current Consumption         | Typical 50 mA           |
| Power Consumption           | $\leq 1.0 \text{ W}$    |
| Start-Up Time               | $< 250 \text{ ms}$      |
| Clock Input                 | RS 422, via Optocoupler |
| Clock Frequency             | 100 kHz – 2 MHz         |
| Reverse Polarity Protection | Yes                     |
| Short Circuit Protection    | Yes                     |
| EMC: Emitted Interference   | DIN EN 61000-6-4        |
| EMC: Noise Immunity         | DIN EN 61000-6-2        |

Data Sheet

Printed at 28-09-2017 01:09



# POSITAL

## FRABA

|      |                   |
|------|-------------------|
| MTTF | 350 years @ 40 °C |
|------|-------------------|

### Sensor

|                        |                                                           |
|------------------------|-----------------------------------------------------------|
| Technology             | Magnetic                                                  |
| Resolution Singleturn  | 12 bit                                                    |
| Resolution Multiturn   | 20 bit                                                    |
| Multiturn Technology   | Self powered magnetic pulse counter (no battery, no gear) |
| Accuracy (INL)         | $\pm 0.0878^\circ$ ( $\leq 12$ bit)                       |
| Sense Signal (Default) | Clockwise shaft movement (front view on shaft)            |
| Code                   | Binary                                                    |

### Environmental Specifications

|                            |                                    |
|----------------------------|------------------------------------|
| Protection Class (Shaft)   | IP66/IP67                          |
| Protection Class (Housing) | IP66/IP67                          |
| Operating Temperature      | -40 °C (-40 °F) - +85 °C (+185 °F) |
| Humidity                   | 98% RH, no condensation            |

### Mechanical Data

|                                                                      |                                                                            |
|----------------------------------------------------------------------|----------------------------------------------------------------------------|
| Housing Material                                                     | Steel                                                                      |
| Housing Coating                                                      | Cathodic corrosion protection (>720 hrs salt spray resistance)             |
| Flange Type                                                          | Clamp, $\varnothing$ 58 mm (L)                                             |
| Flange Material                                                      | Aluminum                                                                   |
| Shaft Type                                                           | Solid, Length = 10 mm                                                      |
| Shaft Diameter                                                       | $\varnothing$ 6 mm (0.24")                                                 |
| Shaft Material                                                       | Stainless Steel V2A (1.4305, 303)                                          |
| Max. Shaft Load                                                      | Axial 40 N, Radial 110 N                                                   |
| Minimum Mechanical Lifetime (10 <sup>8</sup> revolutions with Fa/Fr) | 530 (20 N / 40 N), 185 (40 N / 60 N), 130 (40 N / 80 N), 80 (40 N / 110 N) |
| Rotor Inertia                                                        | $\leq 30 \text{ gcm}^2$ [ $\leq 0.17 \text{ oz-in}^2$ ]                    |
| Friction Torque                                                      | $\leq 5 \text{ Ncm}$ @ 20 °C, (7.1 oz-in @ 68 °F)                          |
| Max. Permissible Mechanical Speed                                    | $\leq 3000 \text{ 1/min}$                                                  |
| Shock Resistance                                                     | $\leq 100 \text{ g}$ (half sine 6 ms, EN 60068-2-27)                       |
| Permanent Shock Resistance                                           | $\leq 10 \text{ g}$ (half sine 16 ms, EN 60068-2-29)                       |
| Vibration Resistance                                                 | $\leq 10 \text{ g}$ (10 Hz - 1000 Hz, EN 60068-2-6)                        |
| Length                                                               | 41,7 mm (1.64")                                                            |
| Weight                                                               | 280 g (0.62 lb)                                                            |

Data Sheet

Printed at 28-09-2017 01:09



# POSITAL


## FRABA

### Electrical Connection

|                        |                               |
|------------------------|-------------------------------|
| Connection Orientation | Axial                         |
| Connector              | M23, Male, 12 pin, CCW / left |

### Certification

|                    |                                                 |
|--------------------|-------------------------------------------------|
| Approval           | CE + cULus listed, Industrial Control Equipment |
| Product Life Cycle | Established                                     |



### Connection Plan



| SIGNAL        | PIN NUMBER |
|---------------|------------|
| Power Supply  | 11         |
| GND           | 12         |
| Data+         | 3          |
| Data-         | 4          |
| Clock+        | 2          |
| Clock-        | 1          |
| Preset        | 9          |
| DIR           | 8          |
| Not Connected | 5          |
| Not Connected | 6          |
| Not Connected | 7          |
| Not Connected | 10         |

Connector-View on Encoder



# POSITAL

## FRABA



### [2D Drawing](#)

### Accessories

#### Connectors & Cables

10m PVC Cable, 12pin, Clockwise, f  
15m PVC Cable, 12pin, Clockwise, f  
1m PVC Cable, 12pin, Clockwise, f  
20m PVC Cable, 12pin, Clockwise, f  
5m PVC Cable, 12pin, Clockwise, f  
30m PVC Cable, 12pin, Clockwise, f  
2m PVC Cable, 12pin, Clockwise, f  
M23, 12pin Clockwise, Female  
More

Clamp Disc w/ Eccentric Hole-4pcs  
Clamp Disc w/ Centred Hole-4pcs

Coupling Bellow Type-06-06

Data Sheet

Printed at 28-09-2017 01:09



# POSITAL

---

## FRABA

Coupling Bellow Type-06-10  
Coupling Bellow Type-06-08  
Coupling Bellow Type-06-(3/8")  
Coupling Bellow Type-06-(1/4")  
Coupling Jaw Type-06-06  
Coupling Jaw Type-06-10  
Coupling Jaw Type-06-08  
Coupling Jaw Type-06-12  
Coupling Jaw Type-06-(1/4")  
Coupling Jaw Type-06-(3/8")  
Coupling Disc Type-06-06  
Coupling Disc Type-06-10  
More

Mounting Bracket for Clamping Flange w/ fixtures  
L Mounting Bracket w/ screws  
Mounting Bracket Spring Loaded f. Clamping Flange

### Contact



POSITAL  
Contact Us

The picture and drawing are for general presentation purposes only. Please refer to the "Download" section for detailed technical drawings.  
All dimension in [inch] mm. © FRABA B.V., All rights reserved. We do not assume responsibility for technical inaccuracies or omissions.  
Specifications are subject to change without notice.