# Constant Voltage LED Power Supply





## Product description:

This type of power supply is an exclusively designed stabilized power supply for LED lamp. With constant voltage (CV) technology, it is suitable for constant voltage lamps (12/24VDC) connected in parallels. As an advantage of constant voltage (CV) technology, a switch can be installed between secondary side and lamps.

The built-in protection circuit will shut down the power supply in case of such faults as: open circuit, short circuit, over load or over temperature. The power supply will restart automatically after fault correction.

### Standards:

EN61347-1

EN61347-2-13

EN61547

EN55015

EN61000-3-2

EN61000-3-3

EN62384

EN62493

## **Characteristics:**

- Independent power supply for constant voltage LED lamp
- Class II protection against electric shock from direct and indirect contact
- Super thin
- SELV output
- Open circuit, short circuit, over load and over temperature protection
- No load power consumption≤0.5W
- Efficiency: ≥83.5% (AC230V,full load)

Last update: 13 June, 2017

Page: 1 of 5



## Specifications:


Model		SLT30-12VFG	SLT30-24VFG
Output	turn on time(S)	≤0.5	≤0.5
	output power(W)	30	30
	output votage(V)	12	24
	output voltage tolerance	+/-5%	+/-5%
	ripple voltage(mV)	90(Vp-p)	100(Vp-p)
	working current range(A)	0-2.5	0-1.25
	dimming interface	No	
	dimming range	n/a	
Input	rated supply voltage(Vac)	220-240	220-240
	voltage range(Vac)	198-264	198-264
	line frequency(Hz)	50/60	50/60
	input current(mA)	160	160
	efficiency 2	83.5%	84.5%
	average efficiency ©	79.5%	80.0%
	no load power consumption(W)	≤0.5	≤0.5
	power factor <sup>2</sup>	0.95	0.95
	inrush current(lpk)	18A/180us	18A/180us
Protection	over voltage protection	YES	YES
	short circuit protection	YES	YES
	over temperature protection	YES	YES
	automatic restart	YES	YES
	over load protection	YES	YES
	surge capacity	L-N: 500V	L-N: 500V
Ambient and Life	Ta(℃)	-2050	-2050
	Tc max.(℃)	85	85
	Storage Temperature(°C)	-3080	
	ambient humidity range	5%85%, Not condensing	
	nominal life-time(hrs)	35'000@T	35'000@Tc=85°C
Other -	weight(g)	135	125
	dimensions (L×W×H)(mm)	246x30x16	
	casing material	Plastic	
	housing colour	Grey+Blue	
	type of protection	IP20	
	protection class	Class2	
Note	1. Tolerance:includes set up tolerance, line regulation and load regulation. 2. Tested at full load,230Vac.Refer to "Power Factor" and "EFFICIENT" curve graphs. 3. Calculate the model's average efficiency for each test voltage by testing at 100%, 75%, 50%, and 25% of rated current and then computing the simple arithmetic erage of these four values. 4. All parameters NOT specially mentioned are measured at nominal voltage input, rated load and 25 of ambient temperature. 5. The power supply is considered as a component that will be operated in combination with final equipment. Since EMC performance will be affected by the complete installation, the final equipment manufacturers must re-qualify EMC Directive on the complete installation again.		

Last update: 13 June, 2017


Page: 2 of 5



## Dimensions(mm):



## Wiring diagram:




Last update: 13 June, 2017

Page: 3 of 5



## Electrical curves:





#### note

For constant current power supply,"LOAD" means the percentage of the maximum rated output voltage. For constant voltage power supply,"LOAD" means the percentage of the maximum rated output current.

Last update: 13 June, 2017

Page: 4 of 5



## Sales & Technical Support:

### Self Electronics Co.,Ltd.

Add: No. 1345 Ju Xian Road, Ningbo Hi Tech Park, Ningbo,

Tel: 0086-574-28805765,28805658 (For English Assistance) 0086-574-28805678 (For Chinese Assistance)

Fax: 0086-574-28805656 E-mail: sales@self-ecg.com http://www.self-ecg.com

#### **SELF ELECTRONICS GERMANY GMBH**

Add:August-Horch-Str. 7,51149 Koeln Tel: 0049 2203 18501-0 Fax: 0049 2203 18501-199

E-mail: saleseu@self-electronics.com

### Self Electronics Co., Ltd., Shenzhen Office

Add: Room2007, Xinglang Xuan, Xinghe Mingju, Fuming Road, Futian District, Shenzhen
Tel: 0086-755-83558850, 83558851
Fax: 0086-755-83558840

Last update: 13 June, 2017

Page: 5 of 5



<sup>\*</sup>Due to continuous improvements and innovations, specifications are subjected to change without notice.