



# **VOLTCRAFT®**

## **VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY**

“For more than 25 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft’s success.”

# **8000 SL-80** **SOLAR POWER BANK**

**Nº 1661734**

**CE**

VERSION 04/18

This powerbank is perfectly suitable for charging mobile devices (e.g. tablet computer, smartphone, MP3 player, digital camera, etc.) while absent from home. The built-in rechargeable battery can be charged via USB or via the solar panel. It features a charging status indicator and an LED lamp.

## **HIGHLIGHTS**

**Built-in LiPo rechargeable battery with 8000 mAh //**

**Solar panel for charging the built-in rechargeable battery //**

**LED lamp with blinking light and SOS function //**

**Protected against splash water (IP54) //**

**2 USB charging ports //**

**Charge status indicator //**

**Rubberized case //**



# TECHNICAL DATA

Input voltage/current	5 V/DC, 2 A
Output voltage/current	5 V/DC, 2.1 A (total)
Rechargeable battery	LiPo, 3.7 V, 8000 mAh
Solar panel	mono-crystalline, 0.9 W, 180 mA
Number of LEDs	1
Charge time	approx. 5 h via USB
Colour temperature	9000-12000 K
Protection type	IP54
Cable length	approx. 30 cm
Operating/storage temperature	0 to +45 °C
Dimensions (L x W x H)	140 x 75 x 17 mm
Weight	218 g

# PACKAGE CONTENT

Solar power bank // USB cable // Carabiner // Operating instructions

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau ([www.conrad.com](http://www.conrad.com)).  
All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represent the technical status at the time of printing.