


# Datasheet

Item no. 1662009

V1\_0712\_01\_en

## Foot Switch



<b>Material</b> .....	<b>Metal</b>
<b>Voltage Rating</b> .....	<b>AC220V/380V</b>
<b>Current Rating</b> .....	<b>10A/5A</b>
<b>No. of Pedals</b> .....	<b>Two</b>
<b>Dimension</b> .....	<b>210x178x135 mm</b>
<b>Operating Temperature</b> .....	<b>-25°C~80°C</b>
<b>Operating Humidity</b> .....	<b>45%~85%RH</b>
<b>Storage Temperature</b> .....	<b>-10°C~75°C</b>
<b>Storage Humidity</b> .....	<b>0~80%RH</b>
<b>Tolerance</b> .....	<b>+/- 2.0mm</b>
<b>Terminal Type</b> .....	<b>Screw-In</b>

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).  
 All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data represent the technical status at the time of printing. Changes