

Pritt Stick

# Safety Data Sheet according to (EC) No 1907/2006 as amended

Page 1 of 8

SDS No.: 695498

V001.3 Revision: 15.08.2022

printing date: 14.12.2022

Replaces version from: 14.07.2022

# SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Pritt Stick

## 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Glue stick

#### 1.3. Details of the supplier of the safety data sheet

Henkel Ltd

Adhesives

Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (1442) 278000

ua-productsafety.uk@henkel.com

For Safety Data Sheet updates please visit our website https://mysds.henkel.com/index.html#/appSelection or www.henkel-adhesives.com.

#### 1.4. Emergency telephone number

24 Hours Emergency Tel: +44 0 8701 906777 - For further general health & safety, technical and practical advice on this product, please call +44 (0) 1606 593933 or write to: Technical Services; Henkel Limited; Road 5; Winsford Industrial Estate; Winsford; Cheshire; CW7 3QY- Email: technical.services@henkel.co.uk

#### **SECTION 2: Hazards identification**

#### 2.1. Classification of the substance or mixture

#### Classification (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

# 2.2. Label elements

#### **Label elements (CLP):**

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

#### 2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

Following substances are present in a concentration >= 0.1% and fulfill the criteria for PBT/vPvB, or were identified as endocrine disruptor (ED):

This mixture does not contain any substances in concentration ≥ the concentration limit that are assessed to be a PBT, vPvB or ED.

# **SECTION 3: Composition/information on ingredients**

#### 3.2. Mixtures

#### Declaration of the ingredients according to CLP (EC) No 1272/2008:

Contains no dangerous substances exceeding the limits of the EU-Regulation

#### **SECTION 4: First aid measures**

#### 4.1. Description of first aid measures

General information:

In case of adverse health effects seek medical advice.

Inhalation:

Move to fresh air, consult doctor if complaint persists.

Skin contact

Rinse with running water and soap. Apply replenishing cream. Change all contaminated clothing.

Eve contact

Rinse immediately with plenty of running water, seek medical advice if necessary.

Ingestion:

Rinse mouth and throat. Drink 1-2 glasses of water. Seek medical advice.

# 4.2. Most important symptoms and effects, both acute and delayed

No data available.

### 4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

# **SECTION 5: Firefighting measures**

#### 5.1. Extinguishing media

#### Suitable extinguishing media:

carbon dioxide, foam, powder, water spray jet, fine water spray

#### Extinguishing media which must not be used for safety reasons:

High pressure waterjet

# 5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO) and carbon dioxide (CO2) can be released.

# **5.3.** Advice for firefighters

Wear protective equipment.

Wear self-contained breathing apparatus.

# **SECTION 6: Accidental release measures**

#### 6.1. Personal precautions, protective equipment and emergency procedures

Wear protective equipment.

# 6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

# 6.3. Methods and material for containment and cleaning up

Remove mechanically.

Dispose of contaminated material as waste according to Section 13.

#### 6.4. Reference to other sections

See advice in section 8

# **SECTION 7: Handling and storage**

# 7.1. Precautions for safe handling

No particular measures required.

Hygiene measures:

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

# 7.2. Conditions for safe storage, including any incompatibilities

Store in sealed original container.

Store in a cool, dry place.

Avoid strictly temperatures below + 5 °C and above + 50 °C.

Do not store together with food or other consumables (coffee, tea, tobacco, etc.).

# 7.3. Specific end use(s)

Glue stick

# **SECTION 8: Exposure controls/personal protection**

# 8.1. Control parameters

#### **Occupational Exposure Limits**

Valid for

Great Britain

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>		Short term exposure limit category / Remarks	Regulatory list
Sucrose 57-50-1 [SUCROSE]		10	Time Weighted Average (TWA):		EH40 WEL
Sucrose 57-50-1 [SUCROSE]		20	Short Term Exposure Limit (STEL):	15 minutes	EH40 WEL

# **Occupational Exposure Limits**

Valid for

Ireland

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Sucrose 57-50-1 [SUCROSE]		10	Time Weighted Average (TWA):		IR_OEL
Sucrose 57-50-1 [SUCROSE]		20	Short Term Exposure Limit (STEL):	15 minutes	IR_OEL

#### **Biological Exposure Indices:**

None

#### 8.2. Exposure controls:

Respiratory protection:

Not needed.

Hand protection: Not needed.

Eye protection: Not needed.

# **SECTION 9: Physical and chemical properties**

# 9.1. Information on basic physical and chemical properties

Physical state solid
Delivery form sticks
Colour white
Odor specific

Melting point 63 - 65 °C (145.4 - 149 °F) Solidification temperature Not applicable, Product is a solid.

Initial boiling point 100 °C (212 °F)

Flammability

Explosive limits

Not applicable, Product is a solid.

Flash point

Auto-ignition temperature

The product is not flammable.

Not applicable, Product is a solid.

Not applicable, Product is a solid.

Not applicable, Product is a solid.

Decomposition temperature Not applicable, Substance/mixture is not self-reactive, no

organic peroxide and does not decompose under foreseen

conditions of use

pH 10 - 10,2 free and total alkanility

(20 °C (68 °F); Conc.: 0,1 %; Solvent:

ethanol/water)

Viscosity (kinematic) Not applicable, Product is a solid.

Viscosity, dynamic 4.000 - 7.500 mPa.s TE1002-208; Viscosity by Brookfield

(Brookfield; 80 °C (176 °F); speed of rotation: 20 min-1; Spindle No: 4)

Solubility (qualitative) Partially soluble

(23 °C (73.4 °F); Solvent: Water)

Partition coefficient: n-octanol/water Not applicable Mixture

Vapour pressure 23 hPa

(20 °C (68 °F))

Density 1,18 - 1,23 g/cm3 QP2107.1; Density

(20 °C (68 °F))

Relative vapour density: Not applicable, Product is a solid.

Particle characteristics Particle Size Not applicable, mixture is a paste.

#### **9.2.** Other information

Other information not applicable for this product

# **SECTION 10: Stability and reactivity**

#### 10.1. Reactivity

None if used for intended purpose.

#### 10.2. Chemical stability

Stable under recommended storage conditions.

#### 10.3. Possibility of hazardous reactions

See section reactivity

#### 10.4. Conditions to avoid

None if used for intended purpose.

#### 10.5. Incompatible materials

None if used properly.

# 10.6. Hazardous decomposition products

# None known. **SECTION 11: Toxicological information** General toxicological information: To the best of our knowledge no harmful effects are to be expected if the product is handled and used properly. 1.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008 Acute oral toxicity: No data available. Acute dermal toxicity: No data available. Acute inhalative toxicity: No data available. Skin corrosion/irritation: No data available. Serious eye damage/irritation: No data available. Respiratory or skin sensitization: No data available. Germ cell mutagenicity:

No data available.

# Carcinogenicity

No data available.

# Reproductive toxicity:

No data available.

STOT-single exposure:
No data available.
STOT wongoted exposures
STOT-repeated exposure::
No data available.
Aspiration hazard:
No data available.
11.2 Information on other hazards
not applicable
SECTION 12: Ecological information
General ecological information:  Do not empty into drains, soil or bodies of water.
12.1. Toxicity
Toxicity (Fish):
No data available.
Toxicity (Daphnia):
No data available.
Chronic toxicity to aquatic invertebrates
No data available.
Toxicity (Algae):
No data available.
No data avanable.
Toxicity to microorganisms
No data available.
12.2. Persistence and degradability
No data available.
12.3. Bioaccumulative potential
No data available.

12.4. Mobility in soil

No data available.

#### 12.5. Results of PBT and vPvB assessment

This mixture does not contain any substances that are assessed to be a PBT or vPvB.

#### 12.6. Endocrine disrupting properties

not applicable

#### 12.7. Other adverse effects

No data available.

# **SECTION 13: Disposal considerations**

# 13.1. Waste treatment methods

Product disposal:

Dispose of waste and residues in accordance with local authority requirements.

Disposal of uncleaned packages:

Use packages for recycling only when totally empty.

Waste code 080410

# **SECTION 14: Transport information**

#### 14.1. UN number

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.2. UN proper shipping name

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

# 14.3. Transport hazard class(es)

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

# 14.4. Packing group

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.5. Environmental hazards

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

# 14.6. Special precautions for user

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

# 14.7. Maritime transport in bulk according to IMO instruments

not applicable

# **SECTION 15: Regulatory information**

No information available:

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Ozone Depleting Substance (ODS) (Regulation (EC) No 1005/2009): Not applicable Prior Informed Consent (PIC) (Regulation (EU) No 649/2012): Not applicable Persistent organic pollutants (Regulation (EU) 2019/1021): Not applicable

#### 15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

#### **SECTION 16: Other information**

ED: Substance identified as having endocrine disrupting properties

EU OEL:

EU EXPLD 1:

Substance with a Union workplace exposure limit

EU EXPLD 1:

Substance listed in Annex I, Reg (EC) No. 2019/1148

EU EXPLD 2

Substance listed in Annex II, Reg (EC) No. 2019/1148

SVHC:

Substance of very high concern (REACH Candidate List)

PBT:

Substance fulfilling persistent, bioaccumulative and toxic criteria

PBT/vPvB: Substance fulfilling persistent, bioaccumulative and toxic plus very persistent and very

bioaccumulative criteria

vPvB: Substance fulfilling very persistent and very bioaccumulative criteria

#### **Further information:**

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (ua-productsafety.de@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

#### Dear Customer,

Henkel is committed to creating a sustainable future by promoting opportunities along the entire value chain. If you would like to contribute by switching from a paper to the electronic version of SDS, please contact the local Customer Service representative. We recommend to use a non-personal email address (e.g. SDS@your\_company.com).

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.