

W-Series**WPD 305 3X35/6X25+9X16 3XGY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Product image**Power feed-in**

Our wide range of W-Series terminal blocks with our WPD main line branch terminals, which are optimised to guarantee both convenience and space gains, ensures a secure and convenient connection at the power feed-in.

General ordering data

Type	WPD 305 3X35/6X25+9X16 3XGY
Order No.	1562190000
Version	W-Series, Distribution block, Rated cross-section: Screw connection, Terminal rail / mounting plate
GTIN (EAN)	4050118385274
Qty.	1 pc(s).

W-Series
WPD 305 3X35/6X25+9X16 3XGY

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	106.8 mm	Width (inches)	4.205 inch
Height	70 mm	Height (inches)	2.756 inch
Depth	53.7 mm	Depth (inches)	2.114 inch
Net weight	434 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	130 °C		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Material data

Material	Wemid	Colour	Light Grey
UL 94 flammability rating	V-0		

System specifications

Version	Screw connection	Tightening torque (clamping screw for aluminium conductors)	11.3...35 Nm (35 mm²) / 5.1...16 Nm (16 mm²)
Tightening torque (clamping screw for copper conductors)	3.5 Nm (35 mm²) / 2.5 Nm (25 mm²)	End cover plate required	No
Number of potentials	3	Number of levels	1
No. of clamping points per level	6	Number of potentials per tier	3
Levels cross-connected internally	No	PE connection	No
N-function	No	PE function	No
PEN function	No		

Additional technical data

Installation advice	Terminal rail / mounting plate	Open sides	closed
Type of mounting	Snap-on		

Conductors for clamping (rated connection)

Connection direction	on side	Type of connection	Screw connection
----------------------	---------	--------------------	------------------

Rating data

Rated AC voltage	1,000 V AC	Rated DC voltage	1,000 V DC
Rated current	125 A	Current at maximum wires	125 A
Standards	IEC 60947-7-1, UL 1059		

Classifications

ETIM 5.0	EC001329	ETIM 6.0	EC000897
eClass 6.2	27-14-11-20	eClass 7.1	27-14-11-20
eClass 8.1	27-14-11-20	eClass 9.0	27-14-11-20
eClass 9.1	27-14-11-20		

W-Series WPD 305 3X35/6X25+9X16 3XGY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Product information

Product information	Power distribution block (Bus Bar) also usable for distribution of neutral conductor and function earth.
---------------------	--

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	DE_PT1001_20160419_013_ISSUE01.pdf
Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP


Safety note

Safety notice	Safety Information
---------------	------------------------------------

W-Series WPD 305 3X35/6X25+9X16 3XGY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings



Technical data

Inputs

Number of connections

Solid

Stranded

Flexible with ferrule

Ribbon cable

Torque

Clamping screw

Stripping length

Outputs

Number of connections

Solid

Stranded

Flexible with ferrule

Torque

Clamping screw

Stripping length

No. of poles

Note

IEC 60947-7-1, UL 1059



top	mid./left	mid./mid.	mid./right	bottom
3				
4...35mm ²				
4...35mm ²				
2.5...25mm ²				
M 8				
19mm				
top	mid./left	mid./mid.	mid./right	bottom
9				6
1.5... 16mm ²				2.5...25mm ²
1.5... 16mm ²				2.5...25mm ²
1.5... 10mm ²				1.5... 16mm ²
2.5Nm				2.5Nm
M 6				
12mm				14mm
3				