
## TO220 50W HIGH POWER RESISTORS

## RNP-50U



### Features and Applications

50W high power resistors in TO220 style mold package for through-hole and screw mounting. AEC-Q200 test certified.

Non-inductive design suits high frequency applications and high-speed pulse circuits.

Low, 2.3 °C/W heat resistance from resistor hot spot to flange and long life performance are presented with thin film metallization technology and rejection of plastic adhesive joint.


Wide 20 milliohm to 510kohm wide resistance range, non-inductive impedance characteristic and heat conduction through the insulated metal flange aids circuit designers.

Small size and thin profile suit high-density compact installations.


Complete thermal conduction, heat dissipation design and vibration durable design also available.

Applications include snubber, gate control, bleeder, filter, rush current protection, braking resistors of automotive, rail traction, wind turbine, PV, UPS and motor control inverters.


### Dimensional Specifications (mm)



### Structure and Material



### Ordering Information



Resistance value (\*) is available following modified E24, +E24.

									2.4				
3.6	3.9	4.0	4.3	4.7	5.0	5.1	5.6	6.2	6.8	7.5	8.0	8.2	9.1

Note\*: When ordering, additional ohm resistance notation recommends for keeping out of misunderstanding.

# TO220 50W HIGH POWER RESISTORS


# RNP-50U

### **Specifications**

		RNP-50U		Test Conditions		
Rated Power		50 Watt		-55 °C to 25 °C flange temperature		
Rating Power		1 Watt		Free air.		
Heat Resistance		2.3 °C/W		Hot spot to flange		
Resistance Range	0.02-0.09ohm	0.1-510 k ohm	10-51Kohm	Note 2		
Nominal Resistance	E6	E24+	E24+	Include 2.5, 4.0, 5.0, 8.0 and 16		
TCR, ppm/°C	>250 (H)	100 (A)	50 (C)	Note 3		
Tolerance	5%(J)	1% (F), 5% (J)	+/-1% (F)	1% tolerance at 0.01-0.091 ohm is available optionally.		
Resistor Material	Thic	k Film	Thin Film			
Capacitance		1.69pF		Equivalent parallel capacitance.		
Inductance		9.65nH		Equivalent series inductance		
Operation Temp.		-55 °C to +175 °C				
Max. Operating Volt.	small	er either 700V or $$	$/P \times R$	P is rating power and R resistance		
Withstanding Voltage		2000VAC		Terminal and flange, 60 seconds, 1mA		
Load Life		+/- 1.0 %		25 °C, 90 min. ON, 30 min. OFF, 1000 hours.		
Humidity		+/- 1.0 %		40 C°, 90-95%RH, DC 0.1W, 1000 hours.		
Temp. Cycle		+/- 0.25 %		-55 °C,30 min.,+155 °C,30 min., 5cycles		
Soldering Heat		+/- 0.1 %		350+/-5 °C, 3seconds,		
Solder ability	(	Over 95% of surface	9	230+/-5 °C, 3seconds.		
Insulation Resistance	(	Over 1,000 Meg ohr	n	Between terminals and flange.		
Vibration		+/- 0.25 %		IEC60068-2-6, see note 4		
Weight		2.1 grams				


### Derating

### Rating Power (W)




# Pulse Energy Durability

Applied to RNP-50UC10ohmF Pulse peak power (W) and resistance < 100ohm




## Temperature Rise

Temperature Rise °C)



### Frequency Characteristics

Impedance (ohm)



- Insulation material is unnecessary between flange and heat-sink, flange and resistor is separated by alumina substrate. Resistance measurement shall be made at a point 5.27mm +/-0.6 mm from the resistor body.
- TCR of low resistance will be increased as 300ppm/0.02ohm, 200ppm/0.05ohm, 140ppm/0.1ohm and 80ppm/0.2ohm typically. Testing point is at 5.27mm from bottom of molding of terminals.

  Test method is IEC60068-2-6, and specification is sine sweep wave form, 100Hz-2000Hz, 10 cycles, amplitude 0.75mm or 100m/s²,
- (4)90minutes. direction x-y z, Amplitude 0.75mm will be applied under break point Frequency (about 60Hz) and 100m/ s2 over break
- When mounting resistor on heat-sink by screw, clip and pressure strip with using heat conduction grease on back side of resistor are recommended. Recommended screw torque is 0.5-0.6Nm.

  Standard packaging is anti-static PE tray, which contains 100pcs / tray.
- (6)

20161101