



VOLTCRAFT®

VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

“Since 1982, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft’s success.”

16000 SL-160

SOLAR POWER BANK

N° 1661732

CE

VERSION 12/21

This powerbank is perfectly suitable for charging mobile devices (e.g. tablet computer, smartphone, MP3 player, digital camera, etc.) while absent from home. The built-in rechargeable battery can be charged via USB or via the solar panel. It features a charging status indicator and an LED lamp. The powerbank is protected against temporary immersion in water (max. 30 minutes up to 1 m depth), when the covers are closed.

HIGHLIGHTS

Built-in LiPo rechargeable battery with 16000 mAh //

Waterproof for max. 30 minutes up to 1 m depth (IP67) //

Solar panel for charging the built-in rechargeable battery //

LED lamp with blinking light and SOS function //

2 USB charging ports (2.4 A + 1 A) //

Charge status indicator //

Rubberized case //



TECHNICAL DATA

Input voltage/current	5 V/DC, 2 A
Output voltage/current	5 V/DC, 3.4 A (total)
Rechargeable battery	LiPo, 16000 mAh
Solar charging current	280 mA
Charge time	approx. 10 h via USB
Colour temperature	9000-12000 K
Protection type	IP67
Operating/storage temperature	0 to +45 °C
Dimensions (L x W x H)	166 x 82 x 20 mm
Weight	356 g

PACKAGE CONTENT

Solar power bank // USB cable // Carabiner // Operating instructions

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represent the technical status at the time of printing.