


MEGAFLEX® 500

halogen-free, flame retardant, oil resistant, UV resistant, flexible, meter marking



Technical data

- Halogen-free flexible control cable adapted to
DIN VDE 0285-525-3-11 /
DIN EN 50525-3-11,
to UL Style 20939, UL Std.758
- **Temperature range**
flexing -30°C to +80°C
fixed installation -40°C to +80°C
- **Nominal voltage**
U₀/U 300/500 V
UL/CSA 600 V
- **Test voltage** 3000 V
- **Minimum bending radius**
flexing 10x cable Ø
fixed installation 4x cable Ø
- **Flexibility**
Alternate bending test acc. to
DIN VDE 0473-396 / DIN EN 50396

Cable structure

- Bare copper conductor, to
DIN VDE 0295 cl.5, fine wire,
BS 6360 cl.5, IEC 60228 cl.5
- Core insulation of halogen-free
special polymer
- Core identification to DIN VDE 0293
black cores with continuous white
numbering
- GN-YE conductor, 3 cores and above
in the outer layer
- Cores stranded in layers with
optimal lay length
- Outer sheath of halogen-free
special polymer
- Sheath colour: grey (RAL 7001)
- With meter marking
- **LS0H**= Low Smoke Zero Halogen

Note

- G = with GN-YE conductor
x = without GN-YE conductor (OZ)
- Also available as a 0,6/1 kV cable
MEGAFLEX® 600
- AWG sizes are approximate equivalent
values. The actual cross section is in mm².
- Screened analogue type:

MEGAFLEX® 500-C

Properties

- Highly flame retardant
- Resistant to oils and greases
- Resistant to UV and weathering
- Hydrolysis resistant
- Flexible, abrasion- and wear-resistant
- Ozone-resistant, recyclable
- The materials used during manufacturing
are cadmium-free, contain no silicone
and are free from substances harmful
to the wetting properties of lacquers

Tests

- Flame test acc. to DIN VDE 0482-332-3-24,
BS 4066 part 3, DIN EN 60332-3-24,
IEC 60332-3-24 (previously DIN VDE 0472
part 804 test method C)
- Self-extinguishing and flame retardant
acc. to DIN VDE 0482-332-1-2,
DIN EN 60332-1-2, IEC 60332-1-2
(equivalent DIN VDE 0472 part 804
test method B), CSA FT1
- Corrosiveness of combustion gases
acc. to NF X 10-702
- Halogen-free acc. to
DIN VDE 0482-754-1,
DIN EN 60754-1, IEC 60754-1
(previously DIN VDE 0482-267-2-1)
- Smoke density acc. to DIN VDE 0482
part 1034-1+2, DIN EN 61034-1+2,
IEC 61034-1+2, BS 7622 part 1+2
- Oil resistant to DIN VDE 0473-811-404/
DIN EN 60811-404
- Hydrolysis resistant to DIN EN 61234-1
- Ozone resistant to
DIN VDE 0473-811-403/DIN EN 60811-403

Application

For fixed installation or flexible application, with free movements without forcing which do not constantly recur and without tensile stress, for high mechanical strain. As a measuring and control cable primarily in machinery and plant construction, in air-conditioning systems, at the warehouse and conveyor systems, in ship-building and in the renewable energies such as in the construction of wind power stations.

CE = Product conforms with Low-Voltage Directive 2014/35/EU.

Part no.	No. cores x cross-sec. mm ²	AWG-No.	Outer Ø app. mm	Cop. weight kg / km	Weight app. kg / km
13344	2 x 0,5	20	5,0	9,6	43,0
13345	3 G 0,5	20	5,3	14,4	50,0
13346	3 x 0,5	20	5,3	14,4	50,0
13347	4 G 0,5	20	5,7	19,0	60,0
13348	4 x 0,5	20	5,7	19,0	60,0
13349	5 G 0,5	20	6,2	24,0	71,0
13350	5 x 0,5	20	6,2	24,0	71,0
13351	7 G 0,5	20	7,4	33,6	84,0

Part no.	No. cores x cross-sec. mm ²	AWG-No.	Outer Ø app. mm	Cop. weight kg / km	Weight app. kg / km
13352	8 G 0,5	20	8,0	38,0	101,0
13353	10 G 0,5	20	8,8	48,0	121,0
13354	12 G 0,5	20	9,1	58,0	142,0
13355	16 G 0,5	20	10,0	76,0	183,0
13356	18 G 0,5	20	10,7	86,0	204,0
13357	20 G 0,5	20	11,2	96,0	227,0
13359	25 G 0,5	20	12,7	120,0	283,0
13360	30 G 0,5	20	13,5	144,0	324,0

Continuation ►

MEGAFLEX® 500

halogen-free, flame retardant, oil resistant, UV resistant, flexible, meter marking



Part no.	No. cores x cross-sec. mm²	AWG-No.	Outer Ø app. mm	Cop. weight kg / km	Weight app. kg / km
13361	34 G 0,5	20	14,5	163,0	367,0
13362	37 G 0,5	20	14,5	178,0	381,0
13363	41 G 0,5	20	15,8	197,0	417,0
13364	42 G 0,5	20	15,8	202,0	454,0
13365	50 G 0,5	20	17,3	240,0	519,0
13366	61 G 0,5	20	18,5	293,0	635,0
13367	65 G 0,5	20	19,4	312,0	694,0
13368	2 x 0,75	19	5,4	14,4	47,0
13369	3 G 0,75	19	5,7	21,6	56,0
13370	3 x 0,75	19	5,7	21,6	56,0
13371	4 G 0,75	19	6,2	29,0	69,0
13372	4 x 0,75	19	6,2	29,0	69,0
13373	5 G 0,75	19	6,8	36,0	83,0
13374	5 x 0,75	19	6,8	36,0	83,0
13375	7 G 0,75	19	8,1	50,0	114,0
13376	7 x 0,75	19	8,1	50,0	114,0
13377	8 G 0,75	19	8,9	58,0	136,0
13378	10 G 0,75	19	9,6	72,0	172,0
13379	12 G 0,75	19	9,9	86,0	183,0
13380	16 G 0,75	19	11,2	115,0	241,0
13381	18 G 0,75	19	11,9	130,0	266,0
13382	20 G 0,75	19	12,6	144,0	291,0
13383	25 G 0,75	19	14,1	180,0	374,0
13384	30 G 0,75	19	15,4	216,0	450,0
13385	34 G 0,75	19	16,4	245,0	517,0
13386	37 G 0,75	19	16,4	260,0	541,0
13387	41 G 0,75	19	17,6	296,0	611,0
13388	42 G 0,75	19	17,6	302,0	621,0
13389	50 G 0,75	19	19,8	360,0	742,0
13390	61 G 0,75	19	20,9	439,0	853,0
13392	65 G 0,75	19	21,8	468,0	909,0
13393	2 x 1	18	5,7	19,2	63,0
13394	3 G 1	18	6,0	29,0	74,0
13395	3 x 1	18	6,0	29,0	74,0
13396	4 G 1	18	6,6	38,4	90,0
13397	4 x 1	18	6,6	38,4	90,0
13398	5 G 1	18	7,2	48,0	109,0
13399	7 G 1	18	8,6	67,0	151,0
13400	8 G 1	18	9,4	77,0	184,0
13401	10 G 1	18	10,4	96,0	224,0
13402	12 G 1	18	10,7	115,0	243,0
13403	16 G 1	18	12,0	154,0	314,0
13404	18 G 1	18	12,7	173,0	361,0
13405	20 G 1	18	13,5	192,0	387,0
13406	25 G 1	18	15,2	240,0	496,0
13407	34 G 1	18	17,4	326,0	670,0
13408	37 G 1	18	17,4	355,0	713,0
13409	41 G 1	18	18,9	394,0	784,0
13410	42 G 1	18	18,9	403,0	824,0
13411	50 G 1	18	21,0	480,0	952,0
13412	61 G 1	18	22,2	586,0	1140,0
13413	65 G 1	18	23,2	628,0	1201,0
13414	2 x 1,5	16	6,3	29,0	70,0
13415	3 G 1,5	16	6,6	43,0	94,0
13416	3 x 1,5	16	6,6	43,0	94,0
13417	4 G 1,5	16	7,2	58,0	112,0
13418	5 G 1,5	16	7,9	72,0	141,0
13419	7 G 1,5	16	9,5	101,0	191,0
13420	8 G 1,5	16	10,4	115,0	224,0
13421	10 G 1,5	16	11,3	144,0	282,0
13422	12 G 1,5	16	11,7	173,0	311,0
13423	16 G 1,5	16	13,3	230,0	392,0
13425	18 G 1,5	16	14,0	259,0	450,0
13426	20 G 1,5	16	14,9	288,0	497,0

Part no.	No. cores x cross-sec. mm²	AWG-No.	Outer Ø app. mm	Cop. weight kg / km	Weight app. kg / km
13427	25 G 1,5	16	16,8	360,0	630,0
13428	34 G 1,5	16	19,4	490,0	842,0
13429	37 G 1,5	16	19,4	533,0	897,0
13430	50 G 1,5	16	23,4	720,0	1277,0
13431	61 G 1,5	16	24,8	878,0	1460,0
13432	65 G 1,5	16	25,8	936,0	1612,0
13433	2 x 2,5	14	7,6	48,0	118,0
13434	3 G 2,5	14	8,3	72,0	151,0
13435	4 G 2,5	14	9,1	96,0	181,0
13436	5 G 2,5	14	10,2	120,0	224,0
13437	7 G 2,5	14	12,1	168,0	316,0
13438	8 G 2,5	14	13,2	192,0	370,0
13439	10 G 2,5	14	14,6	240,0	451,0
13440	12 G 2,5	14	15,2	288,0	499,0
13441	16 G 2,5	14	16,8	384,0	720,0
13442	18 G 2,5	14	18,1	432,0	769,0
13443	20 G 2,5	14	19,0	480,0	911,0
13444	25 G 2,5	14	22,2	600,0	1047,0
13445	30 G 2,5	14	22,9	720,0	1280,0
13446	2 x 4	12	9,2	77,0	199,0
13447	3 G 4	12	9,9	115,0	247,0
13448	4 G 4	12	11,0	154,0	299,0
13449	5 G 4	12	12,1	192,0	369,0
13450	7 G 4	12	13,3	269,0	463,0
13451	8 G 4	12	15,9	307,0	601,0
13452	10 G 4	12	17,3	384,0	698,0
13453	12 G 4	12	18,3	461,0	790,0
13454	16 G 4	12	20,2	614,0	1130,0
13455	18 G 4	12	21,8	691,0	1280,0
13456	2 x 6	10	10,8	115,0	266,0
13457	3 G 6	10	11,7	173,0	360,0
13458	4 G 6	10	13,0	230,0	429,0
13459	5 G 6	10	14,5	288,0	529,0
13460	7 G 6	10	16,0	403,0	631,0
13461	2 x 10	8	14,0	192,0	440,0
13462	3 G 10	8	15,0	288,0	550,0
13463	4 G 10	8	16,8	384,0	708,0
13464	5 G 10	8	18,7	480,0	862,0
13465	7 G 10	8	20,6	672,0	1124,0
13466	2 x 16	6	16,5	307,0	642,0
13467	3 G 16	6	17,6	461,0	830,0
13468	4 G 16	6	19,7	641,0	1060,0
13469	5 G 16	6	21,9	768,0	1270,0
13470	7 G 16	6	24,4	1075,0	1794,0
13471	3 G 25	4	22,5	720,0	1190,0
13472	4 G 25	4	25,2	960,0	1594,0
13473	5 G 25	4	27,9	1200,0	2014,0
13474	3 G 35	2	26,3	1008,0	1590,0
13475	4 G 35	2	28,5	1344,0	2200,0
13476	5 G 35	2	31,2	1680,0	2693,0
13477	3 G 50	1	30,2	1440,0	2571,0
13478	4 G 50	1	34,0	1920,0	3087,0
13479	5 G 50	1	37,8	2400,0	3980,0
13480	3 G 70	2/0	37,0	2016,0	3207,0
13481	4 G 70	2/0	41,5	2688,0	4077,0
13482	5 G 70	2/0	46,2	3360,0	5501,0
13483	3 G 95	3/0	41,4	2736,0	4708,0
13484	4 G 95	3/0	46,2	3648,0	5590,0
13485	5 G 95	3/0	51,5	4560,0	6972,0
13486	3 G 120	4/0	45,7	3456,0	5515,0
13487	4 G 120	4/0	51,2	4608,0	7100,0
13488	3 G 150	300 kcmil	52,8	4320,0	6279,0
13489	4 G 150	300 kcmil	58,3	5760,0	7781,0

Dimensions and specifications may be changed without prior notice. (RA03)