

TEMPERATURE AND HUMIDITY SENSOR



TECHNICAL SPECIFICATIONS

Power source: Solar panel
 Temperature range: 0°C to 40°C
 Humidity range: 0 to 100% RH
 Wall mounting:
 adhesive bounding (included)
 or screws (not included)
 Optional CR1216 battery (not included) for dark area use (3 years in total darkness)
 Operational temperature: 0°C to 40°C
 Radio: EnOcean® Protocol
 EEP: A5-04-01
 Frequency: depending on region
 Range: 30m indoor
 Dimensions: 80*26*18mm

PRODUCT REFERENCE

Frequency 868,3 MHz - STPH-2-1-05 - EAN: 3700313921241 - White

Frequency 908,42 MHz - STPH-2US-1-05 - EAN: 3700313921296 - White

CERTIFICATIONS AND STANDARDS - EUROPE

EN 60950-1: 2006+A11:2009
 +A1:2010+A12:2011+A2:2013
 EN301489-3 V1.6.1
 EN 61000-3-2:2013,
 EN 61000-3-3:2013
 EN 300220-2 V3.1.1
 EN 62479:2010

CERTIFICATIONS AND STANDARDS - USA

FCC & IC Rules

