



Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 11

Tangit KS Cleaner Tissues

SDS No. : 41928
V002.0

Revision: 25.04.2019

printing date: 13.04.2021

Replaces version from: 14.11.2017

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Tangit KS Cleaner Tissues

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:
cleaning tissue

1.3. Details of the supplier of the safety data sheet

Henkel AG & Co. KGaA
Henkelstr. 67
40589 Düsseldorf

Germany

Phone: +49 211 797 0
Fax-no.: +49 211 798 2009

ua-productsafety.de@henkel.com

1.4. Emergency telephone number

The Henkel information service also provides an around-the-clock telephone service on phone no.+49-(0)211-797-3350 for exceptional cases.

Further information is available at Poison Control Centers.

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

Flammable solids	Category 1
H228 Flammable solid.	
Serious eye irritation	Category 2
H319 Causes serious eye irritation.	

2.2. Label elements

Label elements (CLP):

Hazard pictogram:



Signal word:

Danger

Hazard statement: H228 Flammable solid.
H319 Causes serious eye irritation.

Precautionary statement: P101 If medical advice is needed, have product container or label at hand.
P102 Keep out of reach of children.
P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P280 Wear eye protection/face protection.
P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P403+P233 Store in a well-ventilated place. Keep container tightly closed.
P501 Dispose of contents/container in accordance with national regulation.

2.3. Other hazards

Solvents contained in the product evaporate during processing and their vapors can form explosive/highly inflammable air/vapor mixtures.

Pregnant women should absolutely avoid inhalation and skin contact.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

General chemical description:

Cleaner

Base substances of preparation:

Ethanol

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Ethanol 64-17-5	200-578-6 01-2119457610-43	60- 80 %	Eye Irrit. 2 H319 Flam. Liq. 2 H225

For full text of the H - statements and other abbreviations see section 16 "Other information".

Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information:

In case of adverse health effects seek medical advice.

Inhalation:

Move to fresh air, consult doctor if complaint persists.

Skin contact:

Rinse with running water and soap. Apply replenishing cream. Change all contaminated clothing.

Eye contact:

Immediately flush eyes with soft jet of water or eye rinse solution for at least 5 minutes. If pains remain (intensive smarting, sensitivity to light, visual disturbance) continue flushing and contact/seek doctor or hospital.

Ingestion:

Rinse mouth and throat. Drink 1-2 glasses of water. Seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

Causes serious eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures**5.1. Extinguishing media****Suitable extinguishing media:**

carbon dioxide, foam, powder, water spray jet, fine water spray

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO) and carbon dioxide (CO₂) can be released.

5.3. Advice for firefighters

Wear protective equipment.

Wear self-contained breathing apparatus.

Additional information:

Cool endangered containers with water spray jet.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Ensure adequate ventilation.

Keep away from sources of ignition.

Wear protective equipment.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

Remove mechanically.

Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Ventilate working rooms thoroughly. Avoid naked flames, sparking and sources of ignition. Switch off electrical devices. Do not smoke, do not weld. Do not empty waste into waste water drains.

During processing and drying after adhesion, ventilate well. Avoid all sources of fire such as stoves and ovens. Switch off all electrical devices such as parabolic heaters, hot plates, storage heaters etc. in good time for them to have cooled down before commencing work. Avoid all sparks, including those occurring at electrical switches and devices.

Hygiene measures:

Do not eat, drink or smoke while working.

Wash hands before work breaks and after finishing work.

7.2. Conditions for safe storage, including any incompatibilities

Keep only in original container.

Close the container carefully after use and store it at a good ventilated place.

Store protected from heat influence.

Temperatures between + 5 °C and + 35 °C

Do not store together with food or other consumables (coffee, tea, tobacco, etc.).

7.3. Specific end use(s)
cleaning tissue

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational Exposure Limits

Valid for
Germany

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Ethanol 64-17-5			Short Term Exposure Classification:	Category II: substances with a resorptive effect.	TRGS 900
Ethanol 64-17-5	200	380	Exposure limit(s):	4 If the AGW and BGW values are complied with, there should be no risk of reproductive damage (see Number 2.7).	TRGS 900

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Ethanol 64-17-5	aqua (freshwater)		0,96 mg/l				
Ethanol 64-17-5	aqua (marine water)		0,79 mg/l				
Ethanol 64-17-5	aqua (intermittent releases)		2,75 mg/l				
Ethanol 64-17-5	sewage treatment plant (STP)		580 mg/l				
Ethanol 64-17-5	sediment (freshwater)				3,6 mg/kg		
Ethanol 64-17-5	sediment (marine water)				2,9 mg/kg		
Ethanol 64-17-5	Soil				0,63 mg/kg		
Ethanol 64-17-5	oral				380 mg/kg		

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Ethanol 64-17-5	Workers	dermal	Long term exposure - systemic effects		343 mg/kg	
Ethanol 64-17-5	Workers	inhalation	Long term exposure - systemic effects		950 mg/m ³	
Ethanol 64-17-5	General population	dermal	Long term exposure - systemic effects		206 mg/kg	
Ethanol 64-17-5	General population	inhalation	Long term exposure - systemic effects		114 mg/m ³	
Ethanol 64-17-5	General population	oral	Long term exposure - systemic effects		87 mg/kg	

Biological Exposure Indices:

None

8.2. Exposure controls:**Respiratory protection:**

Suitable breathing mask when there is inadequate ventilation.

Combination filter: ABEKP (EN 14387)

This recommendation should be matched to local conditions.

Hand protection:

In the case of longer contact protective gloves made from nitrile rubber are recommended according to EN 374.

Perforation time > 10 minutes

material thickness > 0.1 mm

In the case of longer and repeated contact please note that in practice the penetration times may be considerably shorter than those determined according to EN 374. The protective gloves must always be checked for their suitability for use at the specific workplace (e.g. mechanical and thermal stress, product compatibility, antistatic effects, etc.). The gloves must be replaced immediately at the first signs of wear and tear. The information provided by the manufacturers and given in the relevant trade association regulations for industrial safety must always be observed. We recommend that a hand care plan is drawn up in cooperation with a glove manufacturer and the trade association in accordance with the local operating conditions.

Eye protection:

Goggles which can be tightly sealed.

Protective eye equipment should conform to EN166.

Skin protection:

Suitable protective clothing

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions.

Personal protective equipment should conform to the relevant EN standard.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance	nonwoven fabric thin white
Odor	alcohol-like
Odour threshold	No data available / Not applicable
pH	No data available / Not applicable
Melting point	No data available / Not applicable
Solidification temperature	No data available / Not applicable
Initial boiling point	78,0 °C (172.4 °F)
Flash point	12 °C (53.6 °F); no method
Evaporation rate	No data available / Not applicable
Flammability	No data available / Not applicable
Explosive limits	
lower	1,5 % (V)
upper	15 % (V)
Vapour pressure	No data available / Not applicable
Relative vapour density:	No data available / Not applicable
Density	No data available / Not applicable
Bulk density	No data available / Not applicable
Solubility	No data available / Not applicable
Solubility (qualitative)	Partially miscible
(20 °C (68 °F); Solvent: Water)	
Partition coefficient: n-octanol/water	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Decomposition temperature	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable

Explosive properties
Oxidising properties

No data available / Not applicable
No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity

10.1. Reactivity

None if used for intended purpose.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

None if used for intended purpose.

10.5. Incompatible materials

None if used properly.

10.6. Hazardous decomposition products

None known.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute oral toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Ethanol 64-17-5	LD50	10.470 mg/kg	rat	OECD Guideline 401 (Acute Oral Toxicity)

Acute dermal toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Ethanol 64-17-5	LD50	> 2.000 mg/kg	rabbit	OECD Guideline 402 (Acute Dermal Toxicity)

Acute inhalative toxicity:

The toxicity of the product is due to its narcotic effect after inhalation.
In the event of protracted or repeated exposure, damage to health cannot be excluded.

Hazardous substances CAS-No.	Value type	Value	Test atmosphere	Exposure time	Species	Method
Ethanol 64-17-5	LC50	124,7 mg/l	vapour	4 h	rat	OECD Guideline 403 (Acute Inhalation Toxicity)

Skin corrosion/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Ethanol 64-17-5	not irritating		rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

Serious eye damage/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Ethanol 64-17-5	irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)
Ethanol 64-17-5	not irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

Respiratory or skin sensitization:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Test type	Species	Method
Ethanol 64-17-5	not sensitising	Guinea pig maximisation test	guinea pig	OECD Guideline 406 (Skin Sensitisation)
Ethanol 64-17-5	not sensitising	Mouse local lymphnode assay (LLNA)	mouse	OECD Guideline 429 (Skin Sensitisation: Local Lymph Node Assay)

Germ cell mutagenicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Ethanol 64-17-5	negative	bacterial reverse mutation assay (e.g Ames test)			OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Ethanol 64-17-5	negative	in vitro mammalian chromosome aberration test	without		OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)
Ethanol 64-17-5	negative	mammalian cell gene mutation assay	with and without		OECD Guideline 476 (In vitro Mammalian Cell Gene Mutation Test)
Ethanol 64-17-5	negative				OECD Guideline 475 (Mammalian Bone Marrow Chromosome Aberration Test)

Carcinogenicity

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous components CAS-No.	Result	Route of application	Exposure time / Frequency of treatment	Species	Sex	Method
Ethanol 64-17-5		oral: unspecified		rat		not specified
Ethanol 64-17-5		dermal		mouse	female	not specified
Ethanol 64-17-5		inhalation		mouse	male	not specified

Reproductive toxicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Test type	Route of application	Species	Method
Ethanol 64-17-5	NOAEL P 13.800 mg/kg	Two generation study	oral: unspecified	mouse	OECD Guideline 416 (Two-Generation Reproduction Toxicity Study)

STOT-single exposure:

No data available.

STOT-repeated exposure::

No data available.

Aspiration hazard:

No data available.

SECTION 12: Ecological information**General ecological information:**

Do not empty into drains, soil or bodies of water.

12.1. Toxicity**Toxicity (Fish):**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Ethanol 64-17-5	LC50	14.200 mg/l	96 h	Pimephales promelas	EPA-660 (Methods for Acute Toxicity Tests with Fish, Macroinvertebrates and Amphibians)
Ethanol 64-17-5	NOEC	250 mg/l	120 h	Danio rerio	OECD Guideline 212 (Fish, Short-term Toxicity Test on Embryo and Sac-Fry Stages)

Toxicity (Daphnia):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Ethanol 64-17-5	EC50	5.012 mg/l	48 h	Ceriodaphnia dubia	other guideline:

Chronic toxicity to aquatic invertebrates

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Ethanol 64-17-5	NOEC	9,6 mg/l	9 d	Daphnia magna	not specified

Toxicity (Algae):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Ethanol 64-17-5	EC50	275 mg/l	72 h	Chlorella vulgaris	OECD Guideline 201 (Alga, Growth Inhibition Test)
Ethanol 64-17-5	EC10	11,5 mg/l	72 h	Chlorella vulgaris	OECD Guideline 201 (Alga, Growth Inhibition Test)

Toxicity to microorganisms

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Ethanol 64-17-5	IC50	> 1.000 mg/l	3 h	activated sludge	OECD Guideline 209 (Activated Sludge, Respiration Inhibition Test)

12.2. Persistence and degradability

Hazardous substances CAS-No.	Result	Test type	Degradability	Exposure time	Method
Ethanol 64-17-5	readily biodegradable	aerobic	80 - 85 %	30 d	OECD Guideline 301 D (Ready Biodegradability: Closed Bottle Test)

12.3. Bioaccumulative potential

No data available.

12.4. Mobility in soil

Hazardous substances CAS-No.	LogPow	Temperature	Method
Ethanol 64-17-5	-0,35	24 °C	not specified

12.5. Results of PBT and vPvB assessment

Hazardous substances CAS-No.	PBT / vPvB
Ethanol 64-17-5	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

Dispose of waste and residues in accordance with local authority requirements.

Disposal of uncleaned packages:

Use packages for recycling only when totally empty.

Waste code
140603

SECTION 14: Transport information

14.1. UN number

ADR	3175
RID	3175
ADN	3175
IMDG	3175
IATA	3175

14.2. UN proper shipping name

ADR	SOLIDS CONTAINING FLAMMABLE LIQUID, N.O.S. (Ethanol)
RID	SOLIDS CONTAINING FLAMMABLE LIQUID, N.O.S. (Ethanol)
ADN	SOLIDS CONTAINING FLAMMABLE LIQUID, N.O.S. (Ethanol)
IMDG	SOLIDS CONTAINING FLAMMABLE LIQUID, N.O.S. (Ethanol)
IATA	Solids containing flammable liquid, n.o.s. (Ethanol)

14.3. Transport hazard class(es)

ADR	4.1
RID	4.1
ADN	4.1
IMDG	4.1
IATA	4.1

14.4. Packing group

ADR	II
RID	II
ADN	II
IMDG	II
IATA	II

14.5. Environmental hazards

ADR	not applicable
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

14.6. Special precautions for user

ADR	not applicable Tunnelcode: (E)
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC content	78,00 %
(VOCV 814.018 VOC regulation CH)	

List of ingredients according to Detergents regulation.

Ethanol
1-Propene, homopolymer
Butanone

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

National regulations/information (Germany):

Storage class according to TRGS 510: 4.1B

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H225 Highly flammable liquid and vapor.
H319 Causes serious eye irritation.

Further information:

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (ua-productsafety.de@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.