

**W-Series**  
**WPD 204 2X25/4X16+6X10 2XGY****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com**Product image****Power feed-in**

Our wide range of W-Series terminal blocks with our WPD main line branch terminals, which are optimised to guarantee both convenience and space gains, ensures a secure and convenient connection at the power feed-in.

**General ordering data**

Type	WPD 204 2X25/4X16+6X10 2XGY
Order No.	<a href="#">1562150000</a>
Version	W-Series, Distribution block, Rated cross-section: Screw connection, Terminal rail / mounting plate
GTIN (EAN)	4050118385236
Qty.	1 pc(s).

**W-Series**  
**WPD 204 2X25/4X16+6X10 2XGY**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Width	63 mm	Width (inches)	2.48 inch
Height	68 mm	Height (inches)	2.677 inch
Depth	49 mm	Depth (inches)	1.929 inch
Net weight	202 g		

**Temperatures**

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	130 °C		

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Material data**

Material	Wemid	Colour	Light Grey
UL 94 flammability rating	V-0		

**System specifications**

Version	Screw connection	Tightening torque (clamping screw for aluminium conductors)	5.1 Nm (10 mm <sup>2</sup> )
Tightening torque (clamping screw for copper conductors)	2.5 Nm (25 mm <sup>2</sup> ) / 2 Nm (10 mm <sup>2</sup> )	End cover plate required	No
Number of potentials	1	Number of levels	1
No. of clamping points per level	2	Number of potentials per tier	1
Levels cross-connected internally	Yes	PE connection	No
N-function	No	PE function	No
PEN function	No		

**Additional technical data**

Installation advice	Terminal rail / mounting plate	Open sides	closed
Type of mounting	Snap-on		

**Conductors for clamping (rated connection)**

Connection direction	on side	Type of connection	Screw connection
----------------------	---------	--------------------	------------------

**Rating data**

Rated AC voltage	1,000 V AC	Rated DC voltage	1,000 V DC
Rated current	101 A	Current at maximum wires	101 A
Standards	IEC 60947-7-1, UL 1059		

**Classifications**

ETIM 5.0	EC001329	ETIM 6.0	EC000897
eClass 6.2	27-14-11-20	eClass 7.1	27-14-11-20
eClass 8.1	27-14-11-20	eClass 9.0	27-14-11-20
eClass 9.1	27-14-11-20		

Creation date May 27, 2019 2:01:04 PM CEST

**Data sheet****W-Series  
WPD 204 2X25/4X16+6X10 2XGY**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data****Product information**

Product information Power distribution block (Bus Bar) also usable for distribution of neutral conductor and function earth.

**Approvals**

Approvals



ROHS Conform

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">DE_PT1001_20160419_010_ISSUE01.pdf</a>
Brochure/Catalogue	<a href="#">CAT 1 TERM 16/17 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD</a>
Engineering Data	<a href="#">STEP</a>

**Safety note**


Safety notice [Safety Information](#)

**Data sheet**

**W-Series**  
**WPD 204 2X25/4X16+6X10 2XGY**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



## Technical data

### Inputs

Number of connections

Solid

Stranded

Flexible with ferrule

Ribbon cable

Torque

Clamping screw

Stripping length

### Outputs

Number of connections

Solid

Stranded

Flexible with ferrule

Torque

Clamping screw

Stripping length

No. of poles

### Note

IEC 60947-7-1, UL 1059



top	mid./left	mid./mid.	mid./right	bottom
-----	-----------	-----------	------------	--------

2

2.5...25mm<sup>2</sup>

2.5...25mm<sup>2</sup>

1.5...16mm<sup>2</sup>

M 6

19mm

top	mid./left	mid./mid.	mid./right	bottom
-----	-----------	-----------	------------	--------

6

4

1.5...10mm<sup>2</sup>

1.5...16mm<sup>2</sup>

1.5...10mm<sup>2</sup>

1.5...16mm<sup>2</sup>

1.5...6mm<sup>2</sup>

1.5...10mm<sup>2</sup>

2Nm

2.5Nm

M 5

M 6

12mm

14mm

2