

## HS 2.1-6.4/12 MM W

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

[www.weidmueller.com](http://www.weidmueller.com)



### MultiMark

With MultiMark you have a fast and reliable marking system at your disposal to enable virtually any kind of marking. Connectors, conductors, cables or devices – the MultiMark product family offers a well-structured, practical range of markers which can be used in combination with our advanced M-Print® PRO configuration software for all areas of use.

#### Your benefits with MultiMark

- Compact, practice-oriented range of products
- Quickly printed and assembled
- Reliable identification of your connections
- Excellent material properties

### General ordering data

Type	HS 2.1-6.4/12 MM W
Order No.	<a href="#">2526110000</a>
Version	Conductor and cable markers, 2.1 - 6.4 mm, 12.7 x 11.3 mm, white
GTIN (EAN)	4050118537260
Qty.	4,000 pc(s).
compatible printer	<a href="#">2430920000</a> <a href="#">2448870000</a> <a href="#">1140490000</a>

## HS 2.1-6.4/12 MM W

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

## Technical data

### Dimensions and weights

Width	11.3 mm	Width (inches)	0.445 inch
Height	12.7 mm	Height (inches)	0.5 inch
Depth	0.8 mm	Depth (inches)	0.031 inch
Net weight	0.209 g		

### General data

Colour	white	Halogen	Yes
Material	Polyolefine	Number per roll	4,000 Stück
Operating temperature range	-55...135 °C	Recommended industries	Plant manufacture, Energy, Device manufacturer, Machinery
Width	11.3 mm		

### Conductor and cable markers

Conductor O.D.	2.1 - 6.4 mm	Conductor O.D., max.	6.4 mm
Conductor O.D., min.	2.1 mm	Conductor cross-section, max.	6 mm <sup>2</sup>
Conductor cross-section, min.	1.5 mm <sup>2</sup>	Halogen	Yes
Rate of shrinkage	3:1	Recommended shrinking temperature	90 °C

### Classifications

ETIM 5.0	EC001530	ETIM 6.0	EC001530
eClass 6.2	27-40-04-01	eClass 9.0	27-40-04-01
eClass 9.1	27-40-04-01		

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">EPLAN</a>
------------------	-----------------------

**Data sheet**

**HS 2.1-6.4/12 MM W**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

