

circuit breaker VL800 UL type MG (cat no. LMX3A600) non-interchangeable frame, with circuit breaker approval acc. to UL 489 very high breaking capacity 3-pole; NEMA rating 100kA/480V and 50kA/600V (molded case circuit breaker) trip unit LCD ETU, LI/LS/LSI TA=40°C In=600A, rated current ISD=1.25-10xIR, II=10xIN short-circuit protection IR=200-600A ETU for line protection without auxiliary release without auxiliary/alarm switch



Model	
Type of the driving mechanism / motor drive	No
Design of the overcurrent release	LCD ETU576
General technical data	
Number of poles	3
Size of the circuit-breaker	3VL6 UL
Electrical endurance (switching cycles) / typical	3 000

Usage category	A
Performance class for circuit breaker	N
Mechanical service life (switching cycles) / typical	10 000
Reference code / acc. to DIN 40719 extended according to IEC 204-2 / acc. to IEC 750	Q
Operating frequency / maximum	60 1/s

### Voltage

Rated operational voltage $U_e$ / max.	690 V
Insulation voltage	
• rated value	800 V
• at AC / rated value	800 V
Surge voltage resistance / rated value	8 kV
Operating voltage	
• rated value / maximum	690 V
• for main current circuit / at AC / at 50 Hz / acc. to UL 489 / maximum	600 V
• for main current circuit / at AC / at 50 Hz / maximum	690 V
• for main current circuit / at AC / at 60 Hz / acc. to UL 489 / maximum	600 V
• for main current circuit / at AC / at 60 Hz / maximum	690 V

### Protection class

Protection class IP	IP20
Protective function of the overcurrent release	LSI

### Current

Operating current / at 45 °C / rated value	570 A
Continuous current / rated value	600 A
Derating temperature / for the rated value of the continuous current	50 °C
• acc. to UL 489	40 °C

### Main circuit

Operating frequency	
• 1 / rated value	50 Hz
• 2 / rated value	60 Hz
Operating current	
• at 40 °C / rated value	600 A
• at 50 °C / rated value	570 A
• at 55 °C / rated value	480 A
• at 60 °C / rated value	480 A

### Auxiliary circuit

Number of CO contacts / for auxiliary contacts	0
Number of NC contacts / for auxiliary contacts	0
Number of NO contacts / for auxiliary contacts	0

### Suitability

Suitability for use	system protection
---------------------	-------------------

### Product details

Product component	
<ul style="list-style-type: none"> <li>• Trip indicator</li> <li>• Auxiliary switch</li> <li>• Voltage trigger</li> <li>• undervoltage release</li> <li>• undervoltage release with leading contact</li> </ul>	<p>No</p> <p>No</p> <p>No</p> <p>No</p> <p>No</p>
Product extension / optional / motor drive	Yes

### Product function

Product function	
<ul style="list-style-type: none"> <li>• of thermal overload trip unit</li> <li>• Ground fault protection</li> <li>• for neutral conductors / Short-circuit and overload proof</li> <li>• Overload protection</li> </ul>	<p>adjustable</p> <p>No</p> <p>No</p> <p>Yes</p>

### Short circuit

Operational short-circuit current breaking capacity (Ics)	
<ul style="list-style-type: none"> <li>• at 240 V / rated value</li> <li>• at 415 V / rated value</li> <li>• at 690 V / rated value</li> </ul>	<p>150 kA</p> <p>75 kA</p> <p>10 kA</p>
Maximum short-circuit current breaking capacity (Icu)	
<ul style="list-style-type: none"> <li>• at 240 V / rated value</li> <li>• at 415 V / rated value</li> <li>• at 480 V / acc. to NEMA / rated value</li> <li>• at 600 V / acc. to NEMA / rated value</li> <li>• at 690 V / rated value</li> </ul>	<p>200 kA</p> <p>100 kA</p> <p>100 kA</p> <p>50 kA</p> <p>20 kA</p>

### Connections

Arrangement of electrical connectors / for main current circuit	front side
Type of electrical connection / for main current circuit	without connection accessoires

### Mechanical Design

Height	406.5 mm
Width	190 mm
Depth	176.5 mm

Mounting type	fixed mounting
<ul style="list-style-type: none"> <li>during operation</li> <li>during storage</li> </ul>	-25 ... +70 °C -40 ... +80 °C

### Certificates

Certificate of suitability	UL very high switching capacity (L), non-interchangeable
Reference code	Q
<ul style="list-style-type: none"> <li>acc. to DIN EN 61346-2</li> </ul>	

General Product Approval	EMC	Declaration of Conformity	Test Certificates
--------------------------	-----	---------------------------	-------------------



CSA

[Miscellaneous](#)



UL



C-Tick



EG-Konf.

[Special Test Certificate](#)

Shipping Approval	other
-------------------	-------



RMRS

[Environmental Conformations](#)

[Miscellaneous](#)

[Confirmation](#)

[Manufacturer Declaration](#)

### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mfb=3VL6160-3VH30-0AA0>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3VL6160-3VH30-0AA0>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=3VL6160-3VH30-0AA0](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3VL6160-3VH30-0AA0)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>