

**HS 4.2-12.7/12 MM W****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**MultiMark**

With MultiMark you have a fast and reliable marking system at your disposal to enable virtually any kind of marking. Connectors, conductors, cables or devices – the MultiMark product family offers a well-structured, practical range of markers which can be used in combination with our advanced M-Print® PRO configuration software for all areas of use.

**Your benefits with MultiMark**

- Compact, practice-oriented range of products
- Quickly printed and assembled
- Reliable identification of your connections
- Excellent material properties

**General ordering data**

|                    |                                                                                  |
|--------------------|----------------------------------------------------------------------------------|
| Type               | HS 4.2-12.7/12 MM W                                                              |
| Order No.          | <a href="#">2526150000</a>                                                       |
| Version            | Conductor and cable markers, 4.2 - 12.7 mm, 12.7 x 20.9 mm, white                |
| GTIN (EAN)         | 4050118537307                                                                    |
| Qty.               | 2,000 pc(s).                                                                     |
| compatible printer | <a href="#">2430920000</a> <a href="#">2448870000</a> <a href="#">1140490000</a> |

## HS 4.2-12.7/12 MM W

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

## Technical data

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Width      | 20.9 mm | Width (inches)  | 0.823 inch |
| Height     | 12.7 mm | Height (inches) | 0.5 inch   |
| Depth      | 1.2 mm  | Depth (inches)  | 0.047 inch |
| Net weight | 0.38 g  |                 |            |

### General data

|                             |              |                        |                                                           |
|-----------------------------|--------------|------------------------|-----------------------------------------------------------|
| Colour                      | white        | Halogen                | Yes                                                       |
| Material                    | Polyolefine  | Number per roll        | 2,000 Stück                                               |
| Operating temperature range | -55...135 °C | Recommended industries | Plant manufacture, Energy, Device manufacturer, Machinery |
| Width                       | 20.9 mm      |                        |                                                           |

### Conductor and cable markers

|                               |                   |                                   |                    |
|-------------------------------|-------------------|-----------------------------------|--------------------|
| Conductor O.D.                | 4.2 - 12.7 mm     | Conductor O.D., max.              | 12.7 mm            |
| Conductor O.D., min.          | 4.2 mm            | Conductor cross-section, max.     | 35 mm <sup>2</sup> |
| Conductor cross-section, min. | 6 mm <sup>2</sup> | Halogen                           | Yes                |
| Rate of shrinkage             | 3:1               | Recommended shrinking temperature | 90 °C              |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 5.0   | EC001530    | ETIM 6.0   | EC001530    |
| eClass 6.2 | 27-40-04-01 | eClass 9.0 | 27-40-04-01 |
| eClass 9.1 | 27-40-04-01 |            |             |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                  |                       |
|------------------|-----------------------|
| Engineering Data | <a href="#">EPLAN</a> |
|------------------|-----------------------|

### HS 4.2-12.7/12 MM W

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

