

Circuit breaker Universal current 440 V DC/400 V AC 10kA, 2-pole, C, 16A for railway applications



Model	
Product brand name	SENTRON
Product designation	Miniature circuit breaker
Design of the product	For railway applications
General technical data	
Number of poles	2
Number of poles / Note	2P
Tripping characteristic class	C
Mechanical service life (switching cycles) / typical	10 000
Overtension category	III
Voltage	
Insulation voltage	
<ul style="list-style-type: none"> <li>• at DC / rated value</li> </ul>	250 V
<ul style="list-style-type: none"> <li>• with single-phase operation / at AC / rated value</li> </ul>	440 V
<ul style="list-style-type: none"> <li>• with multi-phase operation / at AC / rated value</li> </ul>	440 V
Supply voltage	
Type of voltage	AC/DC

Current / at AC / rated value	16 A
Supply voltage	
• at AC / rated value	400 V
• at DC / rated value	440 V
Operating voltage	
• at DC / rated value / maximum	500 V
Supply voltage frequency	
• rated value	50/60 Hz

#### Protection class

Protection class IP	IP20, with connected conductors
---------------------	---------------------------------

#### Switching capacity

Switching capacity current	
• at DC / acc. to IEC 60947-2 / rated value	15 kA
• acc. to EN 60898 / rated value	10 kA
Energy limiting class	3

#### Dissipation

Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	1.6 W
---	-------

#### Current

Tripping residual / rated value / derated current / at 40 Cel	15.02 A
Suitability for operation	universal current

#### Product details

Product function / neutral conductor switching	No
Product feature / Touch protection	Yes
Product component	
• combined terminal top	Yes
• combined terminal bottom	Yes
Product feature	
• Properties for main switches in accordance with EN 60204-1	Yes
• halogen-free	Yes
• sealable	Yes
• silicon-free	Yes
Product extension / can be installed / supplementary devices	Yes

#### Short circuit

Breaking capacity short-circuit current (I <sub>cn</sub> )	
• at DC / acc. to EN 60898-2	10 kA

#### Connections

<ul style="list-style-type: none"> <li>Connectable conductor cross-section <ul style="list-style-type: none"> <li>— solid</li> <li>— stranded</li> </ul> </li> <li>Connectable conductor cross-section / finely stranded / with core end processing</li> </ul>	0.75 ... 35 mm <sup>2</sup> 0.75 ... 35 mm <sup>2</sup> 0.75 ... 25 mm <sup>2</sup>
AWG number / as coded connectable conductor cross section	18 ... 4
Tightening torque [lbf·in] / with screw-type terminals	22 ... 31 lbf·in
Tightening torque / with screw-type terminals	2.5 ... 3.5 N·m
Position / of power supply cord	AC as required, observe DC polarity

### Mechanical Design

Height	90 mm
Width	36 mm
Depth	76 mm
Installation depth	70 mm
Number of width units	2
Mounting type	Quick assembly system
Mounting position	any
Net weight	297 g

### Environmental conditions

Influence of the surrounding temperature	max. 95% to 55°C, max. 55% to 70°C, max. 35% to 75°C
Ambient temperature <ul style="list-style-type: none"> <li>during storage</li> </ul>	-40 ... +70 °C -40 ... +75 °C

### Certificates

Reference code <ul style="list-style-type: none"> <li>acc. to DIN EN 61346-2</li> <li>acc. to DIN EN 81346-2</li> </ul>	F F
---	--------

General Product Approval	Declaration of Conformity	Test Certificates	other
--------------------------	---------------------------	-------------------	-------



[Miscellaneous](#)



[Special Test Certificate](#)

[Miscellaneous](#)

### Railway

[Confirmation](#)

### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SY5216-7KK11>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/5SY5216-7KK11>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SY5216-7KK11](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SY5216-7KK11)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



