

standard cabinet 8MF2 HxWxD=2000x 900x 800 Installation: single non-ventilated, assembled, welded IP54,



Figure similar

| Model  |                          |
|--|--------------------------|
| Product brand name                             | SIVACON                  |
| Product designation                            | standard system cubicle  |
| Type of installation                           | stand-alone installation |
| Design of the surface                          | powder-coated            |
| Design of the product / EMC version            | No                       |
| Design of the control cabinet / PC design      | No                       |
| Design of the control cabinet / Console design | No                       |

| Protection class   |  |
|--|--|
| Protection class IP  | IP54   |
| Suitability for installation   |  |
| <ul style="list-style-type: none"> <li>• for inch dimensions</li> <li>• for metric dimensions</li> </ul> | 10-inch, 17-inch, 19-inch, 21-inch, 23-inch, 24-inch<br>M8 |
| Suitability for use / for outside use  | No   |

| Appearance       |             |
|------------------|-------------|
| RAL color number | RAL 7032    |
| Color            | pebble grey |

|                                    |    |
|------------------------------------|----|
| Product component                  |    |
| • removable frame                  | No |
| • Ventilation door                 | No |
| • Mounting plate                   | No |
| • Rear door                        | No |
| • pitched roof                     | No |
| • Viewing door                     | No |
| • height-adjustable mounting plate | No |
| Number of locking devices          | 1  |
| Number of doors                    | 1  |

### Mechanical Design

|  |          |
|--|----------|
| Height   | 2 000 mm |
| Width  | 900 mm   |
| Depth  | 800 mm   |
| Number of modular height units / for installation height | 38       |
| Mounting type  | standing |
| Mounting type / 19-inch installation                     | Yes      |
| Net weight   | 145 kg   |
| Material   | steel    |

### Certificates

|                          |   |
|--------------------------|---|
| Reference code           |   |
| • acc. to DIN EN 61346-2 | U |

| General Product Approval | Declaration of Conformity | other |
|--------------------------|---------------------------|-------|
|--------------------------|---------------------------|-------|



[Miscellaneous](#)

### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF2098-5E>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/8MF2098-5E>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8MF2098-5E](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF2098-5E)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>

