

W-Series
WPD 100 2X25/6X10 GN**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com**Product image****Power distribution**

You safely and efficiently distribute electricity to the power consumers with our W-Series feed-through terminal blocks and our optimised WPD phase distribution blocks.

General ordering data

Type	WPD 100 2X25/6X10 GN
Order No.	1561930000
Version	W-Series, Distribution block, Rated cross-section: Screw connection, Terminal rail / mounting plate
GTIN (EAN)	4050118367300
Qty.	3 pc(s).

W-Series
WPD 100 2X25/6X10 GN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	30.2 mm	Width (inches)	1.189 inch
Height	55.4 mm	Height (inches)	2.181 inch
Depth	49 mm	Depth (inches)	1.929 inch
Net weight	102 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	130 °C		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Material data

Material	Wemid	Colour	green
UL 94 flammability rating	V-0		

System specifications

Version	Screw connection	Tightening torque (clamping screw for aluminium conductors)	4 Nm (16 mm ²) / 4 Nm (25 mm ²)
Tightening torque (clamping screw for copper conductors)	3 Nm (25 mm ²) / 2 Nm (10 mm ²)	End cover plate required	No
Number of potentials	1	Number of levels	1
No. of clamping points per level	2	Number of potentials per tier	1
Levels cross-connected internally	Yes	PE connection	Yes
N-function	No	PE function	No
PEN function	No		

Additional technical data

Installation advice	Terminal rail / mounting plate	Open sides	closed
Type of mounting	Snap-on		

Conductors for clamping (rated connection)

Connection direction	on side	Type of connection	Screw connection
----------------------	---------	--------------------	------------------

Rating data

Rated AC voltage	690 V AC	Rated DC voltage	690 V DC
Rated current	100 A	Current at maximum wires	100 A
Standards	IEC 60998-2-1		

Classifications

ETIM 5.0	EC001329	ETIM 6.0	EC000897
eClass 6.2	27-14-11-20	eClass 7.1	27-14-11-20
eClass 8.1	27-14-11-20	eClass 9.0	27-14-11-20
eClass 9.1	27-14-11-20		

Data sheet**W-Series**
WPD 100 2X25/6X10 GN**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com**Technical data****Approvals**

Approvals



ROHS

Conform

Downloads


Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN_WSCAD
Engineering Data	STEP

Data sheet

W-Series
WPD 100 2X25/6X10 GN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings



Technical data

Inputs

Number of connections
Solid
Stranded
Flexible with ferrule
Ribbon cable
Torque
Clamping screw
Stripping length

Outputs

Number of connections
Solid
Stranded
Flexible with ferrule
Torque
Clamping screw
Stripping length

No. of poles

Note

IEC 60998-2-1

top	mid./left	mid./mid.	mid./right	bottom
	1		1	
	2.5...25mm ²		2.5...25mm ²	
	2.5...25mm ²		2.5...25mm ²	
	1.5...16mm ²		1.5...16mm ²	
	3Nm		3Nm	
	M 6		M 6	
	17mm		17mm	

top	mid./left	mid./mid.	mid./right	bottom
3				3
1.5...10mm ²				1.5...10mm ²
1.5...10mm ²				1.5...10mm ²
1.5...6mm ²				1.5...6mm ²
2Nm				2Nm
M 5				M 5
9mm				9mm

1