

TECHNICAL DATA SHEET

100pcs Heat shrink tube-assortment, shrink ratio 3:1

Item No.: 1698484

This range is particularly suitable for hobbyists, craftsmen, field service, service workshops, electronics and the laboratory needs.

100 pieces of shrinking ration 3:1 standard shrinking tube for a range of application diameter from 1.5 to 18 mm.

Thin wall tubing without internal adhesive in the Black color.

The heat-shrink tubing can be used for insulation, protective covering of components, as anti-kink protection, protection against corrosion, as well as repair of cables and lines, and much more be used.

SCHORUMPFSCHLAUCH-SET 3:1

- GB Heat Shrink Tubing Set 3:1
- FR Jeu de gaines thermo-rétractables 3:1
- NL Krimp slang-set 3:1

Inner-Ø / inner diameter Ø / shillage Ø / diamètre intérieur Ø	Ø nach Schrumpfung / Ø after shrink / Ø apres compression / Ø na het ketspen	Länge / length / pcs / length
1,5 mm	0,5 mm	32 mm
3,0 mm	1,0 mm	32 mm
4,5 mm	1,5 mm	32 mm
6,0 mm	2,0 mm	65 mm
9,0 mm	3,0 mm	65 mm
12,0 mm	4,0 mm	65 mm
15,0 mm	5,0 mm	95 mm
18,0 mm	6,0 mm	95 mm

100 Stück

Distributed by
Conrad Electronic SE
Klaus-Conrad-Str. 1
D-92240 Hirschau


1698484
4 055198 548902

Schrumpfschlauch-Sortiment mit Innenkleber

Schrumpfratio / shrinking ratio: 3:1
Schrumpftemperatur / shrinking temperature: 90°C - 125°C

Inner-Ø	Ø nach Schrumpfung	Länge	Stückzahl
1,5 mm	0,5 mm	32 mm	30
3,0 mm	1,0 mm	32 mm	25
4,5 mm	1,5 mm	32 mm	25
6,0 mm	2,0 mm	65 mm	15
9,0 mm	3,0 mm	65 mm	15
12,0 mm	4,0 mm	65 mm	15
15,0 mm	5,0 mm	95 mm	10
18,0 mm	6,0 mm	95 mm	10

Shrinking ratio	3 : 1
Material	PE
Shrinking temperature	70°C - 120°C
Operation temperature	-40°C - 120°C
Flammability	VW-1
Tensile strength	≥ 10.3Mpa
Elongation at break	≥ 300%
Rated voltage	600V
Diselectric strength	≥ 1kv/mm at 30sec.
Volume resistivity	≥ 10¹⁴Ω



set contents

Section	Heat shrink tube		Length	pcs
	Inner diameter Ø	after shrink Ø		
1	12 mm	4 mm	65 mm	5
2	18 mm	6 mm	95 mm	3
3	15 mm	5 mm	95 mm	4
4	3 mm	1 mm	32 mm	25
5	1.5 mm	0.5 mm	32 mm	30
6	9 mm	3 mm	65 mm	8
7	4.5 mm	1.5 mm	32 mm	15
8	6 mm	2 mm	65 mm	10