

Line laser, red, 635nm, 90°, 2.5mW

LI635-2.5-3(8x26)-F100-C4000

Order Number: 70122534

Main Parameters (*)	min	typ	max	Unit
Wavelength		635		nm
Optical Output Power		2.5		mW
Operating Voltage	2.7	3	3.3	V DC
Operating Current	20	32	55	mA
Operating Temperature	-20		50	°C
Storage Temperature	-40		80	°C

Technical Parameters

Lifetime	>5000h
RoHS	yes

Optical Parameters

Beam Shape	Line
Laser Class	1
Divergence	1 - 1.5mrad
Fan Angle	90°
Line Thickness	<0.3mm@100mm
Operating Distance	0.1m
Optics	glass lens AR coated
Laser technology	Single Mode Diode
Focus	fixed (100mm)

Electrical Parameters

Potential of Housing	isolated
Power Supply	LFNT-3

Mechanical Parameters

Size	Ø8x26mm
Material	aluminium
Cable length	4000mm
Wire type	Belden, AWG 28, 2.20mm, SK-20554-604(2CX28AWG)
Output Aperture	5.5mm
Housing Color	black
Weight	3.5g
Stripping of wire	5mm

(*) Over the complete operating temperature range

Features



- Laser Class 1
- Low power consumption
- For medical devices
- Uniform line thickness
- Image processing


Picture




Cable Colors

Ground		green	GND
Positive		red	2.7 - 3.3, typ 3V DC

Drawing



Safety Label



Revision

| 05-NOV-2014