

## Line laser, green, 532nm, 90°, 10mW

LD532-10-24(20x80)-PL-C1500-NT

Order Number: 70124002

Main Parameters (*)	min	typ	max	Unit
Wavelength		532		nm
Optical Output Power		10		mW
Operating Voltage	21.6	24	26.4	V DC
Operating Current	30	50	90	mA
Operating Temperature	15		30	°C
Storage Temperature	-40		80	°C

### Technical Parameters

Lifetime	>10000h
RoHS	yes

### Optical Parameters

Beam Shape	Line
Laser Class	1
Divergence	D - 0.5mrad
Fan Angle	90°
Line Thickness	<1.5mm@3m
Operating Distance	5m
Optics	glass lens AR coated
Beam Mode	TEM00
Laser technology	Solid State (YVO4+KTP)
Stability	+/- 20% @ 15-30°C
Protection Lens	yes
Focus	fixed (3000mm)
Warm up time	<15min

### Electrical Parameters

Potential of Housing	isolated
Connector	2.5 mm DC plug (GND pole inner)

### Mechanical Parameters

Size	Ø20x80mm
Material	aluminium
Cable length	1500mm
Wire type	22AWG, black, 3,6mm
Output Aperture	5mm
Housing Color	black
Weight	87g
Stripping of wire	5mm
Stripping of cable cover	50mm

(\*) Over the complete operating temperature range



### Features

- Operating Voltage 24V DC
- Isolated housing
- Laser Class 1
- Compact size
- Protection lens


### Picture



### Cable Colors

Ground		black	GND
Positive		white	21.6 - 26.4, typ 24V DC

### Safety Label



### Revision

| 05-JAN-2017