

TECHNICAL DATA SHEET

100pcs Adhesive lined Heat shrink tube-assortment, shrink ratio 3:1

Item No.: 1698485

This range is particularly suitable for hobbyists, craftsmen, field service, service workshops, electronics and the laboratory needs.

100 pieces of shrinking ration 3:1 standard shrinking tube for a range of application diameter from 1.6 to 12.7 mm.

Hot-melt adhesive lined tubing in the Black color.

The heat-shrink tubing can be used for insulation, protective covering of components, as anti-kink protection, protection against corrosion, as well as repair of cables and lines, and much more be used.

Schrumpfschlauch-Sortiment
Schrumpfrate: 3:1 (mit Innenkleber)

GB Heat Shrink Tubing Set 3:1
FR Jeu de gaines thermo-rétractables 3:1
NL Krimpplang-set 3:1

Innen Ø / inner diameter Ø / øInnen	Ø nach Schrumpfung / Ø after shrink / Ø apres compression / Ø na het krimpen	Länge / length / pas / lengte
1.6 mm	0.5 mm	32 mm
2.4 mm	0.8 mm	32 mm
3.2 mm	1.0 mm	32 mm
4.8 mm	1.6 mm	65 mm
6.4 mm	2.2 mm	65 mm
9.5 mm	3.2 mm	65 mm
12.7 mm	4.2 mm	95 mm

100 Stück

1698485

696312096


Distributed by: Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau

Schrumpfschlauch-Sortiment mit Innenkleber

Schrumpfrate / shrinking ratio: 3:1
Schrumpf-Temperatur / shrinking temperature: 90°C - 125°C

Innen-Ø	Ø nach Schrumpfung	Länge	Inhalt	Ø nach Schrumpfung	Länge	Inhalt
1.6 mm	0.5 mm	32 mm	25 Stück	1.6 mm	0.5 mm	25 Stück
2.4 mm	0.8 mm	32 mm	20 Stück	2.4 mm	0.8 mm	20 Stück
3.2 mm	1.0 mm	32 mm	20 Stück	3.2 mm	1.0 mm	20 Stück
4.8 mm	1.6 mm	65 mm	3 Stück	4.8 mm	1.6 mm	3 Stück
6.4 mm	2.2 mm	65 mm	8 Stück	6.4 mm	2.2 mm	8 Stück
9.5 mm	3.2 mm	65 mm	4 Stück	9.5 mm	3.2 mm	4 Stück
12.7 mm	4.2 mm	95 mm	3 Stück	12.7 mm	4.2 mm	3 Stück

Shrinking ratio	3 : 1
Material	PE
Shrinking temperature	70°C - 125°C
Operation temperature	-40°C - 125°C
Flammability	VW-1
Tensile strength	≥ 10.4Mpa
Elongation at break	≥ 300%
Rated voltage	600V
Diselectric strength	≥ 1.5kv/mm at 30sec.
Volume resistivity	≥ 10¹⁴Ω



set contents

Section	Heat shrink tube		Length	pcs
	Inner diameter Ø	after shrink Ø		
1	7.9 mm	2.7 mm	65 mm	5
2	12.7 mm	4.2 mm	95 mm	3
3	9.5 mm	3.2 mm	95 mm	4
4	6.4 mm	2.2 mm	65 mm	8
5	1.6 mm	0.5 mm	32 mm	25
6	2.4 mm	0.8 mm	32 mm	20
7	3.2 mm	1.0 mm	32 mm	20
8	4.8 mm	1.6 mm	65 mm	15