

NEOZED, fuse base, D01, 3-pole, 16 A, Un AC: 400 V, Un DC: 250 V



Figure similar

Model	
Product brand name	NEOZED
Product designation	Fuse base
Design of the product	NEOZED fuse base installation
version	Ceramic fuse base with cover
General technical data	
Number of poles	3
Size of fuse system / acc. to DIN EN 60269-1	D01
Supply voltage	
Operating voltage / rated value	400 V
Dissipation	
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	0.6 W
Main circuit	
Operating current / rated value	16 A

Product details

Product component / Cover Yes

Mechanical Design

Height	54 mm
Width	80.8 mm
Depth	40 mm
Mounting type	DIN rail
Net weight	216 g
Material / of D fuse base	porcelain

Certificates

Reference code	
• acc. to DIN EN 61346-2	F
• acc. to DIN EN 81346-2	F

General Product Approval

Declaration of Conformity



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SG5553>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SG5553>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SG5553

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

