

Switch 230/400 V 1-pole 40 A



Figure similar

Model	
Product brand name	SENTRON
Product designation	ON and OFF switch
Design of the operating mechanism	toggle handle
Type of the driving mechanism / motor drive	No
General technical data	
Number of poles	1
Type of device	other
Supply voltage	
Current / at AC / rated value	40 A
Operating voltage / at AC / at 50/60 Hz / rated value	230 V
Protection class	
Protection class IP	IP20
Current	
Continuous current / rated value	40 A

Auxiliary circuit	
Number of CO contacts / for auxiliary contacts	0
Number of NC contacts / for auxiliary contacts	0
Number of NO contacts / for auxiliary contacts	1

Suitability	
Suitability for integration / Distribution board	Yes
<b>Suitability for use</b>	
• Main switch	No
• switch disconnecter	Yes
• EMERGENCY OFF switch	No
• safety switch	No
• maintenance/repair switch	No

Product details	
Product feature / interlock	No
Product extension / optional	
• motor drive	No
• Voltage trigger	No

Connections	
Type of electrical connection / for main current circuit	screw-type terminals

Mechanical Design	
Mounting type	standard rail
Mounting type	
• front mounting with 4-hole attachment	No
• central front mounting	No

Certificates		
<b>Declaration of Conformity</b>	<b>Test Certificates</b>	<b>other</b>



[Miscellaneous](#)

[Environmental Confirmations](#)

### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5TE2411-0>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/5TE2411-0>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5TE2411-0](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TE2411-0)

**CAX-Online-Generator**  
<http://www.siemens.com/cax>

**Tender specifications**  
<http://www.siemens.com/specifications>