

Switch disconnecter with fuses In-line design, pluggable NH00 160 A, 4-pole Standard switching capacity S manual operation without auxiliary switch without current transformer without ammeter

Model	
Product brand name	SENTRON
version	With double disconnection
Design type	plug-in to busbars with 185mm center-line spacing
Type of ammeter	without
Type of switching contact / double breaking switching contact	Yes
Design of the load switch / Strip form	Yes
Type of the driving mechanism	manual operating mechanism

General technical data	
Number of poles	4
Field of application	LINE PROTECTION
Size of disconnecting link	00
Size of fuse link	00
power factor cos phi / in utilization category	
• AC-21 B / at 400 V	0.95
• AC-22 B / at 400 V	0.65
• AC-22 B / at 500 V	0.65
circuit-breaker / Design	3NJ620
Reference code / acc. to DIN 40719 extended according to IEC 204-2 / acc. to IEC 750	Q
Fuse system	LV HRC fuse

Voltage	
Rated operational voltage Ue / max.	690 V
Rated insulation voltage Ui	1 000 V
Insulation voltage / rated value	1 000 V
Surge voltage resistance / rated value	8 000 V
Operating voltage	
• at AC / at 50/60 Hz / rated value	690 V

Protection class	
Protection class IP	IP41

Current	
rated current In	
• max.	160 A

<ul style="list-style-type: none"> • at 35 Cel • at 40 Cel • at 45 Cel • at 50 Cel 	160 A 152 A 144 A 136 A
Continuous current / rated value	160 A
Let-through current / I _{2t} / maximum permissible / in utilization category	
<ul style="list-style-type: none"> • AC-21 B / at 400 V • AC-21 B / at 500 V • AC-22 B / at 400 V • AC-22 B / at 500 V 	223 000 A ² ·s 223 000 A ² ·s 223 000 A ² ·s 223 000 A ² ·s
Let-through current / I _c / maximum permissible / in utilization category	
<ul style="list-style-type: none"> • AC-21 B / at 400 V • AC-21 B / at 500 V • AC-22 B / at 400 V • AC-22 B / at 500 V 	55 000 A 55 000 A 55 000 A 55 000 A
Accuracy class / of the current transformer	without

Short circuit

Maximum short-circuit current breaking capacity (I _{cu}) / at 400 V / rated value	55 kA
---	-------

Connections

Type of connection, main circuit	Stud terminal, M8
Type of electrical connection / for main current circuit	stud terminals

Mechanical Design

Height	99 mm
Width	590 mm
Depth	308 mm
Type of mounting	plug-in version
Mounting type	pluggable
Busbar center-to-center spacing	185 mm
Busbar center-to-center spacing	
<ul style="list-style-type: none"> • 40 mm • 50 mm • 60 mm • 100 mm • 185 mm 	No No No No Yes

Environmental conditions

Installation altitude / at height above sea level / maximum	2 000 m
<ul style="list-style-type: none"> • during operation 	-25 ... +55 °C

Certificates

Reference code

- acc. to DIN EN 61346-2

Q

General Product Approval	Declaration of Conformity	other
--------------------------	---------------------------	-------

[Miscellaneous](#)



EG-Konf.

[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mfb=3NJ6204-1AA00-0AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NJ6204-1AA00-0AA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NJ6204-1AA00-0AA0

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>