

SIPLUS NET SCALANCE X204-2 -40...+60°C for medial exposure based on 6GK5204-2BB10-2AA3 . Managed IE switch, 4x 10/100 Mbit/s RJ45 ports, 2x 100 Mbit/s multimode BFOC, LED diagnostics, error signaling contact with set button, Redundant power supply, PROFINET IO device, network management, integr. redundancy manager, incl. electron. Manual on CD-ROM, C-plug optional



<b>Product type designation</b>	<b>X204-2</b>
<b>Transmission rate</b>	
Transfer rate	10 Mbit/s, 100 Mbit/s
<b>Interfaces / for communication / integrated</b>	
Number of electrical connections	
<ul style="list-style-type: none"> <li>for network components or terminal equipment</li> </ul>	4
<b>Interfaces / others</b>	
Number of electrical connections	
<ul style="list-style-type: none"> <li>for signaling contact</li> </ul>	1
<ul style="list-style-type: none"> <li>for power supply</li> </ul>	1
<ul style="list-style-type: none"> <li>for redundant voltage supply</li> </ul>	1
Type of electrical connection	
<ul style="list-style-type: none"> <li>for signaling contact</li> </ul>	2-pole terminal block
<ul style="list-style-type: none"> <li>for power supply</li> </ul>	4-pole terminal block
design of the removable storage	
<ul style="list-style-type: none"> <li>C-PLUG</li> </ul>	Yes
<b>Signal-Inputs/outputs</b>	

Operating voltage / of the signaling contacts	
<ul style="list-style-type: none"> <li>• at DC / Rated value</li> </ul>	24 V
Operating current / of the signaling contacts	
<ul style="list-style-type: none"> <li>• at DC / maximum</li> </ul>	0.1 A

#### Supply voltage, current consumption, power loss

Type of voltage / of the supply voltage	DC
Supply voltage	
<ul style="list-style-type: none"> <li>• external</li> </ul>	24 V
<ul style="list-style-type: none"> <li>• external / minimum</li> </ul>	18 V
<ul style="list-style-type: none"> <li>• external / maximum</li> </ul>	32 V
Product component / fusing at power supply input	Yes
Fuse protection type / at input for supply voltage	0.6 A / 60 V
Consumed current / maximum	0.215 A
Power loss [W]	
<ul style="list-style-type: none"> <li>• at DC / at 24 V</li> </ul>	6.36 W

#### Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> <li>• during operation</li> </ul>	-40 ... +60 °C
<ul style="list-style-type: none"> <li>• during storage</li> </ul>	-40 ... +70 °C
<ul style="list-style-type: none"> <li>• during transport</li> </ul>	-40 ... +70 °C
Relative humidity	
<ul style="list-style-type: none"> <li>• at 25 °C / without condensation / during operation / maximum</li> </ul>	100 %
<ul style="list-style-type: none"> <li>• with condensation / maximum</li> </ul>	100 %; rel. humidity, incl. condensation/frost permissible (no commissioning in condensed state)
Ambient condition / relating to ambient temperature - air pressure - installation altitude	-40 ... +60 °C at 1080 hPa ... 795 hPa (-1000 m ... +2000 m) // -40 ... +50 °C at 795 hPa ... 658 hPa (+2000 m ... +3500 m) // -40 ... +40 °C at 658 hPa ... 540 hPa (+3500 m ... +5000 m)
Resistance to biologically active substances / conformity acc. to EN 60721-3-3	Yes; Compliance with EN 60721-3-3, Class 3B2 mold, fungus, and sponge spores (except fauna). The supplied plug covers must remain in place over the unused interfaces during operation!
Resistance to chemically active substances / conformity acc. to EN 60721-3-3	Yes; Compliance with EN 60721-3-3, class 3C4 incl. salt spray according to EN 60068-2-52 (severity 3). The supplied plug covers must remain in place over the unused interfaces during operation!
Resistance to mechanically active substances / conformity acc. to EN 60721-3-3	Yes; Compliance with EN 60721-3-3, Class 3S4 including sand, dust. The supplied plug covers must remain in place over the unused interfaces during operation!
Protection class IP	IP30

#### Design, dimensions and weight

Design	compact
Width	60 mm
Height	125 mm

Depth	124 mm
Net weight	0.78 kg
Mounting type	
<ul style="list-style-type: none"> <li>• 35 mm DIN rail mounting</li> <li>• wall mounting</li> <li>• S7-300 rail mounting</li> </ul>	<p>Yes</p> <p>Yes</p> <p>Yes</p>

### Product properties, functions, components / general

Cascading in the case of a redundant ring / at reconfiguration time of <math>\leq 0.3\text{ s}</math>	50
Cascading in cases of star topology	any (depending only on signal propagation time)

### Product functions / management, configuration

Product function	
<ul style="list-style-type: none"> <li>• CLI</li> <li>• web-based management</li> <li>• MIB support</li> <li>• TRAPs via email</li> <li>• Configuration with STEP 7</li> <li>• SMTP server</li> <li>• Port mirroring</li> <li>• with IRT / PROFINET IO switch</li> <li>• PROFINET IO diagnosis</li> </ul>	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>No</p> <p>Yes</p>
Product function / switch-managed	Yes
Protocol / is supported	
<ul style="list-style-type: none"> <li>• Telnet</li> <li>• HTTP</li> <li>• HTTPS</li> <li>• TFTP</li> <li>• FTP</li> <li>• BOOTP</li> <li>• GMRP</li> <li>• DCP</li> <li>• LLDP</li> <li>• SNMP v1</li> <li>• SNMP v2</li> <li>• SNMP v3</li> <li>• IGMP (snooping/querier)</li> </ul>	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>No</p> <p>No</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>No</p>

### Product functions / Diagnosis

Product function	
<ul style="list-style-type: none"> <li>• Port diagnostics</li> <li>• Statistics Packet Size</li> <li>• Statistics packet type</li> </ul>	<p>Yes</p> <p>Yes</p> <p>Yes</p>

• Error statistics	Yes
<b>Product functions / DHCP</b>	
Product function	
• DHCP client	Yes
<b>Product functions / Redundancy</b>	
Product function	
• Ring redundancy	Yes
• High Speed Redundancy Protocol (HRP)	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	No
Protocol / is supported / Media Redundancy Protocol (MRP)	Yes
Product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• Passive listening	Yes
<b>Product functions / Security</b>	
Protocol / is supported	
• SSH	Yes
<b>Product functions / Time</b>	
Product function	
• SICLOCK support	Yes
Protocol / is supported	
• NTP	No
• SNTP	Yes
<b>Standards, specifications, approvals</b>	
Standard	
• for hazardous zone	EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
• for emitted interference	EN 61000-6-4 (Class A)
• for interference immunity	EN 61000-6-2
<b>Standards, specifications, approvals / CE</b>	
Certificate of suitability / CE marking	Yes
<b>Standards, specifications, approvals / miscellaneous</b>	
Certificate of suitability	EN 61000-6-2, EN 61000-6-4
• Railway application in accordance with EN 50155	No

- Railway application in accordance with EN 50124-1
- KC approval

No

Yes

### Standards, specifications, approvals / ship classification

#### Marine classification association

- American Bureau of Shipping Europe Ltd. (ABS)
- Bureau Veritas (BV)
- Det Norske Veritas (DNV)
- Germanische Lloyd (GL)
- Lloyds Register of Shipping (LRS)
- Nippon Kaiji Kyokai (NK)
- Polski Rejestr Statkow (PRS)

No

No

No

No

No

No

No

### Further Information / Internet Links

#### Internet-Link

- to website: Selector SIMATIC NET SELECTION TOOL
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<http://www.siemens.com/snst>

<http://www.siemens.com/simatic-net>

<https://mall.industry.siemens.com>

<http://www.siemens.com/industry/infocenter>

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

### Security information

#### Security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

**last modified:**

08/27/2019