

Miniature circuit breaker 400 V 6kA, 2-pole, C, 16A, D=70 mm with screwless outgoing terminals



Model	
Product brand name	SENTRON
Product designation	Miniature circuit breaker
Design of the product	Miniature circuit breaker 5SJ6
General technical data	
Number of poles	2
Number of poles / Note	2P
Tripping characteristic class	C
circuit-breaker / Design	5SJ6
Mechanical service life (switching cycles) / typical	20 000
Overvoltage category	3
Voltage	
Insulation voltage / at AC / rated value	440 V
Supply voltage	
Type of voltage	AC/DC
Current / at AC / rated value	16 A
Supply voltage / at AC / rated value	400 V
Operating voltage	

<ul style="list-style-type: none"> • with multi-phase operation / at AC / maximum 	440 V
<ul style="list-style-type: none"> • at DC / rated value / maximum 	60 V
Supply voltage frequency	
<ul style="list-style-type: none"> • rated value 	50 Hz

Protection class

Protection class IP	IP20, with connected conductors
---------------------	---------------------------------

Switching capacity

Switching capacity current	
<ul style="list-style-type: none"> • acc. to EN 60898 / rated value 	6 kA
<ul style="list-style-type: none"> • acc. to IEC 60947-2 / rated value 	6 kA
Energy limiting class	3

Dissipation

Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	1.9 W
Suitability for operation	Residential buildings/infrastructure

Product details

Product function / neutral conductor switching	No
Product feature / Touch protection	Yes
Product feature	
<ul style="list-style-type: none"> • halogen-free 	Yes
<ul style="list-style-type: none"> • sealable 	Yes
<ul style="list-style-type: none"> • silicon-free 	Yes
Product extension / can be installed / supplementary devices	No

Connections

<ul style="list-style-type: none"> • Connectable conductor cross-section / on plug-type connection / using the upper clamping point / without core end processing 	1.5 ... 4 mm ²
<ul style="list-style-type: none"> • Connectable conductor cross-section <ul style="list-style-type: none"> — solid 	0.75 ... 25 mm ²
<ul style="list-style-type: none"> — stranded 	0.75 ... 25 mm ²
<ul style="list-style-type: none"> • Connectable conductor cross-section / finely stranded / with core end processing 	1.5 ... 2.5 mm ²
Type of electrical connection / Plug-in terminals / Note	Screwless terminals on the outgoing side for 1.5 to 4mm ²

Mechanical Design

Height	90 mm
Width	36 mm
Depth	76 mm
Installation depth	70 mm
Number of width units	2

Mounting position	any
-------------------	-----

Environmental conditions

Influence of the surrounding temperature	Periodically +55°C, max. 95% humidity
Ambient temperature	-25 ... +45 °C
• during storage	-40 ... +75 °C

Certificates

Reference code	
• acc. to DIN EN 61346-2	F
• acc. to DIN EN 81346-2	F

General Product Approval	Declaration of Conformity	Test Certificates
--------------------------	---------------------------	-------------------



[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SJ6216-7KS>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SJ6216-7KS>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SJ6216-7KS

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

