

LV HRC fuse element, NH00, In: 125 A, gG, Un AC: 500 V, Un DC: 250 V, Combined indicator, Insulated grip lugs



Model	
Product brand name	SETRON
Product designation	LV HRC fuse link
Design of the product	With blade contacts
Design of an identification indicator	Combination alarms
Design of the switching contact	Non-corroding, silver-plated
Design of the fuse link	LV HRC fuse link

General technical data	
Size of fuse system / acc. to DIN EN 60269-1	NH00
Operating class of the fuse link	gG
circuit-breaker / Design	3NA6
Type of voltage	AC/DC
Current / at AC / rated value	125 A
Supply voltage	
• at AC / rated value	500 V
• at DC	250 V

Protection class	
Protection class IP	IP20, with connected conductors

## Switching capacity

Switching capacity current	
<ul style="list-style-type: none"> <li>at DC / acc. to IEC 60947-2 / rated value</li> </ul>	25 kA
<ul style="list-style-type: none"> <li>acc. to IEC 60947-2 / rated value</li> </ul>	120 kA

## Dissipation

Power loss [W]	8.9 W
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	8.9 W

## Current

Tripping residual / rated value / derated current / at 40 Cel	118.75 A
Diken-export / Let-through energy	DE_3NA_00_500_gG_125

## Mechanical Design

Width	
<ul style="list-style-type: none"> <li>of the enclosure</li> </ul>	30 mm
Mounting position	Any, preferably vertical
Net weight	202 g

## Environmental conditions

Ambient temperature	-5 ... +40 °C
<ul style="list-style-type: none"> <li>during storage</li> </ul>	Air humidity 90% at 20 °C
Environmental category	-20 to +50 at 95% relative humidity

## Certificates

Reference code	
<ul style="list-style-type: none"> <li>acc. to DIN EN 61346-2</li> </ul>	F
<ul style="list-style-type: none"> <li>acc. to DIN EN 81346-2</li> </ul>	F

### General Product Approval

### Declaration of Conformity

### Test Certificates



[Special Test Certificate](#)

[Type Test Certificates/Test Report](#)

### Test Certificates

### Shipping Approval

### other

[Miscellaneous](#)



GL

[Miscellaneous](#)

## Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NA6832>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3NA6832>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**



[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NA6832](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NA6832)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



1

-F1



2