

Contactor, 3-pole, 1200 A/AC-1 Main contacts 3 NO Auxiliary contacts 3 NO + 2 NC, AC operation 220-240 V AC, 50/60 Hz

Protection class IP on the front	IP00
Reference code acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750	K
Reference code acc. to DIN EN 81346-2	Q
Reference code acc. to DIN EN 61346-2	Q
Number of poles for main current circuit	3
Number of NO contacts for main contacts	3
Number of NC contacts for main contacts	0
Operating current <ul style="list-style-type: none"> • at AC-1 at 400 V <ul style="list-style-type: none"> — at ambient temperature 40 °C rated value • at AC-3 at 400 V rated value 	1 200 A 700 A
Operating power <ul style="list-style-type: none"> • at AC-1 at 400 V rated value • at AC-3 at 400 V rated value 	655 kW 370 kW
Type of voltage of the control supply voltage	AC
Control supply voltage at AC <ul style="list-style-type: none"> • at 50 Hz rated value 	240 ... 208 V
Control supply voltage frequency <ul style="list-style-type: none"> • 1 rated value • 2 rated value 	50 Hz 50 Hz
Control version of the switch operating mechanism	conventional
Number of NC contacts for auxiliary contacts <ul style="list-style-type: none"> • instantaneous contact • lagging switching 	2 0
Number of NO contacts for auxiliary contacts <ul style="list-style-type: none"> • instantaneous contact • leading contact 	2 0
Identification number and letter for switching elements	22
Mounting type <ul style="list-style-type: none"> • Side-by-side mounting 	screw fixing Yes
Height	272 mm
Width	266 mm
Depth	225.5 mm
Type of electrical connection	

- for main current circuit
- for auxiliary and control current circuit

screw-type terminals
screw-type terminals

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

www.siemens.com/sirius/catalogs

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3TK1832-0AM7>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3TK1832-0AM7>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3TK1832-0AM7>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3TK1832-0AM7&lang=en

Characteristic: Tripping characteristics, I²t, Let-through current

<https://support.industry.siemens.com/cs/ww/en/ps/3TK1832-0AM7/char>

Further characteristics (e.g. electrical endurance, switching frequency)

<http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3TK1832-0AM7&objecttype=14&gridview=view1>

last modified:

09/12/2019