

SITOR fuse link, with slotted blade contacts, NH3, In: 355 A, gR, Un AC: 1000 V, Un DC: 440 V, front indicator



Model	
Product brand name	SETRON
Product designation	SITOR fuse link
Design of the product	With slotted blade contacts
Design of an identification indicator	front indicator
Design of the switching contact	Non-corroding, silver-plated
General technical data	
Size of fuse system / acc. to DIN EN 60269-1	NH3
Operating class of the fuse link	gR
Supply voltage	
Type of voltage	AC/DC
Current / at AC / rated value	355 A
Supply voltage	
• at AC / rated value	1 000 V
• at DC	440 V
Switching capacity	
Switching capacity current	
• acc. to IEC 60947-2 / rated value	100 kA

Product details

Product description Not non-interchangeable

Mechanical Design

Mounting position Any, preferably vertical

Environmental conditions

Ambient temperature -20 ... +50 °C

Environmental category -20 to +50 at 95% relative humidity

Certificates

Reference code

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F
F

Declaration of Conformity

other

[Miscellaneous](#)



EG-Konf.

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NE3434-3C>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NE3434-3C>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NE3434-3C

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

