

SITOR fuse link, with slotted blade contacts, NH3, In: 125 A, aR, Un AC: 2500 V, Un DC: 1500 V, front indicator



Model	
Product brand name	SETRON
Product designation	SITOR fuse link
Design of the product	With slotted blade contacts
Design of an identification indicator	front indicator
Design of the switching contact	With blade contacts, silver-plated
Design of the fuse link	Semiconductor protection fuse link

General technical data	
Size of fuse system / acc. to DIN EN 60269-1	NH3
Operating class of the fuse link	aR
Varying load factor (WL)	1

Supply voltage	
Type of voltage	AC/DC
Current / at AC / rated value	125 A
Supply voltage	
• at AC / rated value	2 500 V
• at DC	1 500 V

### Switching capacity

<b>Switching capacity current</b>	
<ul style="list-style-type: none"> <li>• acc. to IEC 60947-2 / rated value</li> </ul>	100 kA
<b>Product details</b>	
Product description	Not non-interchangeable
<b>Mechanical Design</b>	
Mounting position	Any, preferably vertical
<b>Environmental conditions</b>	
Ambient temperature	-20 ... +50 °C
Environmental category	-20 to +50 at 95% relative humidity
<b>Certificates</b>	
Reference code	
<ul style="list-style-type: none"> <li>• acc. to DIN EN 61346-2</li> </ul>	F
<ul style="list-style-type: none"> <li>• acc. to DIN EN 81346-2</li> </ul>	F
<b>Declaration of Conformity</b>	



EG-Konf.

### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NE9622-1C>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3NE9622-1C>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NE9622-1C](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NE9622-1C)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>

