

8770 Multi-Conductor - Audio, Control and Instrumentation Cable



For more Information
please call

1-800-Belden1



General Description:

18 AWG stranded (16x30) tinned copper conductors, conductors cabled, polyethylene insulation, overall Beldfoil® shield (100% coverage), 20 AWG stranded tinned copper drain wire, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
3	18	16x30	TC - Tinned Copper

Total Number of Conductors: 3

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
PE - Polyethylene	0.4572

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil® (w/ shorting fold)	Tape	Aluminum Foil-Polyester Tape w/Shorting Fold	100.000

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
20	Stranded	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.8382

Overall Cable

Overall Cabling Lay Length & Direction:

Length (mm)	Direction	Twists (twist/m)
68.580	Left Hand	14.436

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	Red
3	Clear

Overall Nominal Diameter: 6.248 mm

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +60°C
UL Temperature Rating:	60°C (UL AWM Style 2093)
Bulk Cable Weight:	53.575 Kg/Km
Max. Recommended Pulling Tension:	329.167 N
Min. Bend Radius/Minor Axis:	63.500 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CM
NEC Articles:	800
CEC/C(UL) Specification:	CM
AWM Specification:	UL Style 2093 (300 V 60°C)
EU Directive 2011/65/EU (ROHS II):	Yes

METRIC MEASUREMENT VERSION

8770 Multi-Conductor - Audio, Control and Instrumentation Cable

EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 UL Loading
CSA Flame Test:	FT1

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	88770

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
69

Nom. Inductance:

Inductance (µH/m)
0.591

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
78.744

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)
157.488

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
21.6546

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
27.8885

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Description	Current
10C temperature rise	5.3 Amps per conductor @ 25°C ambient

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8770 060U1000	1,000 FT	37.000 LB	CHROME		3 #18 LDPE FS PVC
8770 060U500	500 FT	19.000 LB	CHROME		3 #18 LDPE FS PVC
8770 0601000	1,000 FT	39.000 LB	CHROME	C	3 #18 LDPE FS PVC
8770 06010000	10,000 FT	420.000 LB	CHROME	C Y	3 #18 LDPE FS PVC
8770 06010001	10,000 FT	420.000 LB	CHROME	C Z	3 #18 LDPE SH PVC
8770 06012000	12,000 FT	492.000 LB	CHROME	C Y	3 #18 LDPE SH PVC
8770 060500	500 FT	20.000 LB	CHROME	C	3 #18 LDPE FS PVC
8770 0605000	5,000 FT	190.000 LB	CHROME		3 #18 LDPE FS PVC

Notes:

C = CRATE REEL PUT-UP.
 Y = FINAL PUT-UP LENGTH MAY VARY -10% TO +20% FROM LENGTH SHOWN.MAY CONTAIN 2 PIECES. MINIMUM LENGTH OF ANY ONE PIECE IS 1500'.
 Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

8770 Multi-Conductor - Audio, Control and Instrumentation Cable

Revision Number: 3 Revision Date: 08-02-2013

© 2016 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).