




Data sheet | Item number: 2201-1207

2-conductor ground terminal block; with push-button; 1.5 mm²; with test port; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®



www.wago.com/2201-1207



Data

Connection data

Connection technology

Push-in CAGE CLAMP®



| | |
|---|--|
| Actuation type | Push-in Push-button Operating tool |
| Connectable conductor materials | Copper |
| Nominal cross section | 1.5 mm ² |
| Solid conductor | 0.25 ... 2.5 mm ² / 22 ... 14 AWG |
| Solid conductor, push-in termination | 0.75 ... 2.5 mm ² / 18 ... 14 AWG |
| Fine-stranded conductor | 0.25 ... 2.5 mm ² / 22 ... 14 AWG |
| Fine-stranded conductor with ferrule, push-in termination, from | 0.75 mm ² / 18 AWG |
| Strip length | 9 ... 11 mm / 0.35 ... 0.43 Inch |
| Total number of connection points | 2 |
| Total number of potentials | 1 |
| Number of levels | 1 |
| Type of wiring | Front-entry wiring |

Geometrical Data

| | |
|---------------------------------------|----------------------|
| Width | 4.2 mm / 0.165 inch |
| Height from upper-edge of DIN-35 rail | 32.9 mm / 1.295 inch |
| Depth | 50.8 mm / 2 inch |

Mechanical data

| | |
|------------------|---------------------|
| Design | horizontal |
| Type of mounting | DIN-35 rail |
| Marking level | Center/side marking |

Material Data

| | |
|---------------------|----------------------|
| Color | green-yellow |
| Insulating material | Polyamide 66 (PA 66) |
| Weight | 7.005 g |

Commercial data

| | |
|--------------------|---------------|
| Packaging type | BOX |
| Country of origin | DE |
| GTIN | 4055143694674 |
| Customs Tariff No. | 85369010000 |

Approvals / Certificates

Ex-Approvals

| Logo | Approval | Certificate name |
|------|--|------------------|
| | AEx UL International Germany GmbH c/o Physikalisch Technische | E185892 sec. 25 |

Bundesanstalt




ATEX
Physikalisch Technische Bundesanstalt

PTB 18 ATEX 1004 U (II 2 G Ex eb IIC Gb bzw. I M 2 Ex eb I Mb)



IECEX
Physikalisch Technische Bundesanstalt



IECEX PTB 18.0011U (Ex eb IIC Gb and Ex eb I Mb)



IECEX
Physikalisch Technische Bundesanstalt

IECEX PTB 18.0011U (Ex eb IIC Gb and Ex eb I Mb)

Country specific Approvals

| Logo | Approval | Certificate name |
|--|---------------------------------------|------------------|
|  | CCA DEKRA Certification B.V. | NTR NL 7664 |
|  | CSA DEKRA Certification B.V. | 70173738 |
|  | KEMA/KEUR DEKRA Certification B.V. | 71-102875 |

UL-Approvals

| Logo | Approval | Certificate name |
|--|---|------------------|
|  | cURus Underwriters Laboratories Inc. | 4788308064 |

Compatible products

plug

















Item no.: 2002-880
Empty component plug housing; 10.4 mm wide; 2-pole; Type 4

www.wago.com/2002-880

Marking accessories

Item no.: 2009-110
Marking strips; on reel; not stretchable; plain; snap-on type

www.wago.com/2009-110

| | | |
|--|---|--|
|  | Item no.: 2009-114 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type | www.wago.com/2009-114 |
|  | Item no.: 2009-114/000-002 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type | www.wago.com/2009-114/000-002 |
|  | Item no.: 2009-114/000-005 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type | www.wago.com/2009-114/000-005 |
|  | Item no.: 2009-114/000-006 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type | www.wago.com/2009-114/000-006 |
|  | Item no.: 2009-114/000-007 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type | www.wago.com/2009-114/000-007 |
|  | Item no.: 2009-114/000-012 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type | www.wago.com/2009-114/000-012 |
|  | Item no.: 2009-114/000-023 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type | www.wago.com/2009-114/000-023 |
|  | Item no.: 2009-114/000-024 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type | www.wago.com/2009-114/000-024 |
|  | Item no.: 793-4501 WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type | www.wago.com/793-4501 |
|  | Item no.: 793-4501/000-002 WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type | www.wago.com/793-4501/000-002 |
|  | Item no.: 793-4501/000-005 WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type | www.wago.com/793-4501/000-005 |
|  | Item no.: 793-4501/000-006 WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type | www.wago.com/793-4501/000-006 |
|  | Item no.: 793-4501/000-007 WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type | www.wago.com/793-4501/000-007 |
|  | Item no.: 793-4501/000-012 WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type | www.wago.com/793-4501/000-012 |



Item no.: 793-4501/000-017
WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type

www.wago.com/793-4501/000-017



Item no.: 793-4501/000-023
WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type

www.wago.com/793-4501/000-023



Item no.: 793-4501/000-024
WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type

www.wago.com/793-4501/000-024

Carrier rail



Item no.: 210-112
Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to EN 60715; "Hole width 25 mm

www.wago.com/210-112



Item no.: 210-113
Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; unslotted; according to EN 60715

www.wago.com/210-113



Item no.: 210-114
Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; unslotted; similar to EN 60715

www.wago.com/210-114



Item no.: 210-115
Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to EN 60715; "Hole width 18 mm

www.wago.com/210-115



Item no.: 210-118
Steel carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to EN 60715

www.wago.com/210-118



Item no.: 210-196
Aluminum carrier rail; 35 x 8.2 mm; 1.6 mm thick; 2 m long; unslotted; similar to EN 60715

www.wago.com/210-196



Item no.: 210-197
Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; slotted; similar to EN 60715

www.wago.com/210-197



Item no.: 210-198
Copper carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to EN 60715

www.wago.com/210-198

End plate



Item no.: 2002-1291
End and intermediate plate; 0.8 mm thick

www.wago.com/2002-1291



Item no.: 2002-1292
End and intermediate plate; 0.8 mm thick

www.wago.com/2002-1292



Item no.: 2002-1293
Separator plate; 2 mm thick; oversized

www.wago.com/2002-1293



Item no.: 2002-1294
Separator plate; 2 mm thick; oversized

www.wago.com/2002-1294





Insulation stop
















Item no.: 2001-171
Insulation stop; 0.25 - 0.5 mm²; 5 pieces/strip




















www.wago.com/2001-171






ferrule

| | | |
|---|--|--|
|  | Item no.: 216-241 Ferrule; Sleeve for 0.5 mm ² / AWG 22; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90 | www.wago.com/216-241 |
|  | Item no.: 216-242 Ferrule; Sleeve for 0.75 mm ² / AWG 20; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90 | www.wago.com/216-242 |
|  | Item no.: 216-243 Ferrule; Sleeve for 1 mm ² / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90 | www.wago.com/216-243 |
|  | Item no.: 216-244 Ferrule; Sleeve for 1.5 mm ² / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90 | www.wago.com/216-244 |




Jumper

| | | |
|--|--|--|
|  | Item no.: 2001-402 Push-in type jumper bar; insulated; 2-way; Nominal current 18 A | www.wago.com/2001-402 |
|  | Item no.: 2001-403 Push-in type jumper bar; insulated; 3-way; Nominal current 18 A | www.wago.com/2001-403 |
|  | Item no.: 2001-404 Push-in type jumper bar; insulated; 4-way; Nominal current 18 A | www.wago.com/2001-404 |
|  | Item no.: 2001-405 Push-in type jumper bar; insulated; 5-way; Nominal current 18 A | www.wago.com/2001-405 |
|  | Item no.: 2001-405/011-000 Star point jumper; insulated; 3-way (1-3-5); IN = IN terminal block | www.wago.com/2001-405/011-000 |
|  | Item no.: 2001-406 Push-in type jumper bar; insulated; 6-way; Nominal current 18 A | www.wago.com/2001-406 |
|  | Item no.: 2001-406/020-000 Delta jumper; insulated; 1-2 3-4 5-6; IN = IN terminal block | www.wago.com/2001-406/020-000 |
|  | Item no.: 2001-407 Push-in type jumper bar; insulated; 7-way; Nominal current 18 A | www.wago.com/2001-407 |
|  | Item no.: 2001-408 Push-in type jumper bar; insulated; 8-way; Nominal current 18 A | www.wago.com/2001-408 |
|  | Item no.: 2001-409 Push-in type jumper bar; insulated; 9-way; Nominal current 18 A | www.wago.com/2001-409 |
|  | Item no.: 2001-410 Push-in type jumper bar; insulated; 10-way; Nominal current 18 A | www.wago.com/2001-410 |
|  | Item no.: 2001-433 Push-in type jumper bar; insulated; from 1 to 3; Nominal current 18 A | www.wago.com/2001-433 |
|  | Item no.: 2001-434 Push-in type jumper bar; insulated; from 1 to 4; Nominal current 18 A | www.wago.com/2001-434 |

| | | |
|--|--|--|
|  | Item no.: 2001-435 Push-in type jumper bar; insulated; from 1 to 5; Nominal current 18 A | www.wago.com/2001-435 |
|  | Item no.: 2001-436 Push-in type jumper bar; insulated; from 1 to 6; Nominal current 18 A | www.wago.com/2001-436 |
|  | Item no.: 2001-437 Push-in type jumper bar; insulated; from 1 to 7; Nominal current 18 A | www.wago.com/2001-437 |
|  | Item no.: 2001-438 Push-in type jumper bar; insulated; from 1 to 8; Nominal current 18 A | www.wago.com/2001-438 |
|  | Item no.: 2001-439 Push-in type jumper bar; insulated; from 1 to 9; Nominal current 18 A | www.wago.com/2001-439 |
|  | Item no.: 2001-440 Push-in type jumper bar; insulated; from 1 to 10; Nominal current 18 A | www.wago.com/2001-440 |
|  | Item no.: 2009-412 Push-in type wire jumper; insulated; wire length 60 mm; Conductor cross section 1.5 mm ² ; suitable for 2001, 2002, 2003 and 2022 Series rail-mounted terminal blocks | www.wago.com/2009-412 |
|  | Item no.: 2009-414 Push-in type wire jumper; insulated; wire length 110 mm; Conductor cross section 1.5 mm ² ; suitable for 2001, 2002, 2003 and 2022 Series rail-mounted terminal blocks | www.wago.com/2009-414 |
|  | Item no.: 2009-416 Push-in type wire jumper; insulated; wire length 250 mm; Conductor cross section 1.5 mm ² ; suitable for 2001, 2002, 2003 and 2022 Series rail-mounted terminal blocks | www.wago.com/2009-416 |
|  | Item no.: 210-103 Wire commoning chain; insulated; 50 connections | www.wago.com/210-103 |
|  | Item no.: 210-123 Wire commoning chain; insulated; 50 connections | www.wago.com/210-123 |
| check | | |
|  | Item no.: 2001-511 Modular TOPJOB®S connector; modular; for jumper contact slot; 1-pole | www.wago.com/2001-511 |
|  | Item no.: 2001-549 Spacer module; modular; e.g., for bridging commoned terminal blocks | www.wago.com/2001-549 |
|  | Item no.: 2001-552 TOPJOB®S connector strip; for jumper contact slot; 2-pole | www.wago.com/2001-552 |
|  | Item no.: 2001-553 TOPJOB®S connector strip; for jumper contact slot; 3-pole | www.wago.com/2001-553 |
|  | Item no.: 2001-554 TOPJOB®S connector strip; for jumper contact slot; 4-pole | www.wago.com/2001-554 |
|  | Item no.: 2001-555 TOPJOB®S connector strip; for jumper contact slot; 5-pole | www.wago.com/2001-555 |
|  | Item no.: 2001-556 TOPJOB®S connector strip; for jumper contact slot; 6-pole | www.wago.com/2001-556 |
|  | Item no.: 2001-557 TOPJOB®S connector strip; for jumper contact slot; 7-pole | www.wago.com/2001-557 |

| | | |
|--|---|--|
|  | Item no.: 2001-558 TOPJOB®S connector strip; for jumper contact slot; 8-pole | www.wago.com/2001-558 |
|  | Item no.: 2001-559 TOPJOB®S connector strip; for jumper contact slot; 9-pole | www.wago.com/2001-559 |
|  | Item no.: 2001-560 TOPJOB®S connector strip; for jumper contact slot; 10-pole | www.wago.com/2001-560 |
|  | Item no.: 2009-174 Test plug adapter; for 4 mm Ø test plugs; for testing TOPJOB®S rail-mounted terminal blocks | www.wago.com/2009-174 |
|  | Item no.: 2009-182 Testing tap; for max. 2.5 mm ² ; tool-free connection for individual test wires 0.08 - 2.5 mm | www.wago.com/2009-182 |

tools

| | | |
|--|--|--|
|  | Item no.: 210-647 Operating tool with partially insulated shaft; Blade (2.5 x 0.4) mm; short | www.wago.com/210-647 |
|  | Item no.: 210-648 Operating tool with partially insulated shaft; Blade (2.5 x 0.4) mm; short; angled | www.wago.com/210-648 |
|  | Item no.: 210-719 Operating tool with partially insulated shaft; Type 1, blade (2.5 x 0.4) mm | www.wago.com/210-719 |

Downloads

Documentation

Bid Text

| | | | |
|-----------|--------------|-----------------|----------|
| 2201-1207 | Aug 15, 2018 | DOCX 15.0 kB | Download |
|-----------|--------------|-----------------|----------|

smartDATA

CAD data

| | | |
|-----------------------|-----|----------|
| 3D Download 2201-1207 | URL | Download |
|-----------------------|-----|----------|

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG
 Hansastr. 27
 32423 Minden
 Phone: +49571 887-0 | Fax: +49571 887-169
 Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
 We are always happy to take your call at +49 (571) 887-44222.