

SICUBE 8MF 2000 EMC cabinet, welding version NI HxWxD=1800x800x 600 mm for stand-alone installation with side panels, IP40



Figure similar

Model	
Product designation	EMC cubicle
Type of installation	stand-alone installation
Design of the surface	frames and enclosure parts nickel-coated, enclosure parts powder-coated on the outside
Design of the product / EMC version	Yes
Design of the control cabinet / PC design	No
Design of the control cabinet / Console design	No
Protection class	
Protection class IP	IP40
Suitability for installation	10-inch, 17-inch, 19-inch, 21-inch, 23-inch, 24-inch
<ul style="list-style-type: none"> <li>• for inch dimensions</li> <li>• for metric dimensions</li> </ul>	M8
Suitability for use / for outside use	No
Appearance	
RAL color number	RAL 7032
Color	pebble grey

Product component	
• removable frame	No
• Ventilation door	No
• Mounting plate	No
• Rear door	No
• pitched roof	No
• Viewing door	No
• height-adjustable mounting plate	No
Number of locking devices	1
Number of doors	1

## Mechanical Design

Height	1 800 mm
Width	800 mm
Depth	600 mm
Number of modular height units / for installation height	34
Mounting type	standing
Mounting type / 19-inch installation	Yes
Net weight	111.3 kg
Material	steel

## Certificates

Reference code	
• acc. to DIN EN 61346-2	U
<b>General Product Approval</b>	<b>other</b>

[Miscellaneous](#)



## Further information

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF2886-4EN>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MF2886-4EN>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8MF2886-4EN](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF2886-4EN)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>