

Residual current operated circuit breaker, 2-pole, type B+, short-time delayed, In: 16 A, 300 mA, Un AC: 230 V



Model	
Product brand name	SENTRON
Product designation	RCCB
Design of the product	Short-time delayed
General technical data	
Number of poles	2
Size of installation devices / acc. to DIN 43880	1
Protection against electrical shock	Finger and back-of-hand safe
Short-circuit current rating	10 kA
circuit-breaker / Design	5SM3
Mechanical service life (switching cycles) / typical	10 000
Switching function / short-term delayed	Yes
Overvoltage category	III
Supply voltage	
Current / at AC / rated value	16 A
<ul style="list-style-type: none"> Supply voltage / at AC / rated value 	230 V
<ul style="list-style-type: none"> Supply voltage / for testing equipment / minimum 	195 V

- rated value

50 Hz

Protection class

Protection class IP	IP20, if the distribution board is installed, with connected conductors
---------------------	---

Switching capacity

Switching capacity current / according to IEC 61008-1 / rated value	0.8 kA
---	--------

Dissipation

Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	0.4 W
---	-------

Current

Tripping residual current / rated value	300 mA
---	--------

Tripping residual / rated value / derated current

• at 40 Cel	16 A
• at 45 Cel	16 A
• at 50 Cel	15.36 A
• at 55 Cel	14.72 A
• at 60 Cel	14.08 A
• at 65 Cel	13.44 A
• at 70 Cel	12.8 A

Type of fault current	B+
-----------------------	----

I ² t-value / permissible	70 000 A ² ·s
--------------------------------------	--------------------------

Surge current resistance / rated value	3 kA
--	------

Operating frequency	50/60Hz
---------------------	---------

Product details

Product feature / silicon-free	Yes
--------------------------------	-----

Product extension / can be installed / supplementary devices	Yes
--	-----

Connections

Connectable conductor cross-section

• solid	1.5 ... 25 mm ²
• stranded	1.5 ... 25 mm ²

Tightening torque / with screw-type terminals	2.5 ... 3 N·m
---	---------------

Position / of power supply cord	Top or bottom (bottom for SIGRES function also in switched-off state)
---------------------------------	---

Mechanical Design

Height	90 mm
--------	-------

Width	72 mm
-------	-------

Depth	70 mm
-------	-------

Installation depth	70 mm
--------------------	-------

Number of width units	4
-----------------------	---

Mounting type	DIN rail (REG)
Mounting position	any
Net weight	570 g

Environmental conditions

Ambient temperature	-25 ... +45 °C
• during storage	-40 ... +75 °C

Certificates

Reference code	
• acc. to DIN EN 61346-2	F
• acc. to DIN EN 81346-2	F

General Product Approval	Declaration of Con- formity	other
---------------------------------	--	--------------



[Miscellaneous](#)



[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SM3621-4KK14>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SM3621-4KK14>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SM3621-4KK14

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>