

Miniature circuit breaker 400 V 6kA, 3+N-pole B, 20 A, D=70 mm



Model	
Product brand name	SENTRON
Product designation	Miniature circuit breaker
General technical data	
Number of poles	4
Number of poles / Note	3P+N
Tripping characteristic class	B
circuit-breaker / Design	5SY6
Mechanical service life (switching cycles) / typical	10 000
Oversvoltage category	III
Voltage	
Insulation voltage	
<ul style="list-style-type: none"> <li>• with single-phase operation / at AC / rated value</li> </ul>	440 V
<ul style="list-style-type: none"> <li>• with multi-phase operation / at AC / rated value</li> </ul>	440 V
Supply voltage	
Type of voltage	AC
Current / at AC / rated value	20 A

Supply voltage	
<ul style="list-style-type: none"> <li>• at AC / rated value</li> </ul>	400 V
Operating voltage	
<ul style="list-style-type: none"> <li>• at DC / rated value / maximum</li> </ul>	72 V
Supply voltage frequency	
<ul style="list-style-type: none"> <li>• rated value</li> </ul>	50/60 Hz

Protection class	
Protection class IP	IP20, with connected conductors

Switching capacity	
Switching capacity current	
<ul style="list-style-type: none"> <li>• at DC / acc. to IEC 60947-2 / rated value</li> </ul>	15 kA
<ul style="list-style-type: none"> <li>• acc. to EN 60898 / rated value</li> </ul>	6 kA
<ul style="list-style-type: none"> <li>• acc. to IEC 60947-2 / rated value</li> </ul>	15 kA
Energy limiting class	3

Dissipation	
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	2.2 W

Current	
Tripping residual / rated value / derated current / at 40 Cel	19.04 A
Suitability for operation	Mechanical engineering / industry

Product details	
Product function / neutral conductor switching	Yes
Product feature / Touch protection	Yes
Product component	
<ul style="list-style-type: none"> <li>• combined terminal top</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• combined terminal bottom</li> </ul>	Yes
Product feature	
<ul style="list-style-type: none"> <li>• Properties for main switches in accordance with EN 60204-1</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• halogen-free</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• sealable</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• silicon-free</li> </ul>	Yes
Product extension / can be installed / supplementary devices	Yes

Short circuit	
Breaking capacity short-circuit current (Icn)	
<ul style="list-style-type: none"> <li>• at AC / acc. to UL 1077 and CSA C22.2 No.235</li> </ul>	5 kA

Connections	
<ul style="list-style-type: none"> <li>• Connectable conductor cross-section</li> </ul>	

— solid	0.75 ... 35 mm <sup>2</sup>
— stranded	0.75 ... 35 mm <sup>2</sup>
• Connectable conductor cross-section / finely stranded / with core end processing	0.75 ... 25 mm <sup>2</sup>
AWG number / as coded connectable conductor cross section	18 ... 4
Tightening torque [lbf-in] / with screw-type terminals	22 ... 31 lbf-in
Tightening torque / with screw-type terminals	2.5 ... 3.5 N·m
Position / of power supply cord	Any

### Mechanical Design

Height	90 mm
Width	72 mm
Depth	76 mm
Installation depth	70 mm
Number of width units	4
Mounting type	Quick assembly system
Mounting position	any
Net weight	630 g

### Environmental conditions

Influence of the surrounding temperature	max. 95% to 55°C, max. 55% to 70°C, max. 35% to 75°C
Ambient temperature	-25 ... +55 °C
• during storage	-40 ... +75 °C

### Certificates

Reference code	
• acc. to DIN EN 61346-2	F
• acc. to DIN EN 81346-2	F

### General Product Approval



[Miscellaneous](#)



Declaration of Conformity	Test Certificates	Shipping Approval
---------------------------	-------------------	-------------------



[Miscellaneous](#)



### Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SY6620-6>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/5SY6620-6>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SY6620-6](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SY6620-6)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>





