

RC unit for 5SP4, 4-pole, type A, In: 100 A, 30 mA, Un AC: 400 V



Model	
Product brand name	SENTRON
Product designation	RC unit
Design of the product	Instantaneous
Product variations	for 5SP4
General technical data	
Number of poles	4
Size of installation devices / acc. to DIN 43880	1
Protection against electrical shock	Finger and back-of-hand safe
circuit-breaker / Design	5SM2
Mechanical service life (switching cycles) / typical	10 000
Switching function / short-term delayed	No
Overvoltage category	III
Supply voltage	
Current / at AC / rated value	100 A
<ul style="list-style-type: none"> <li>• Supply voltage / at AC / rated value</li> <li>• Supply voltage / for testing equipment / minimum</li> </ul>	<p>400 V</p> <p>195 V</p>

• rated value

50 Hz

## Protection class

Protection class IP

IP20, if the distribution board is installed, with connected conductors

## Dissipation

Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole

6 W

## Current

Tripping residual current / rated value

30 mA

Tripping residual / rated value / derated current

• at 40 Cel

93 A

• at 45 Cel

93 A

• at 50 Cel

90 A

• at 55 Cel

87 A

• at 60 Cel

85 A

• at 65 Cel

83 A

• at 70 Cel

80 A

Type of fault current

A

Surge current resistance / rated value

1 kA

Operating frequency

50Hz

## Product details

Product feature / silicon-free

Yes

Product extension / can be installed / supplementary devices

Yes

## Connections

Connectable conductor cross-section

• solid

6 ... 50 mm<sup>2</sup>

• stranded

6 ... 50 mm<sup>2</sup>

Tightening torque / with screw-type terminals

2.5 ... 3 N·m

Position / of power supply cord

top or bottom

## Mechanical Design

Height

90 mm

Width

124 mm

Depth

70 mm

Installation depth

70 mm

Number of width units

5

Mounting type

DIN rail (REG)

Mounting position

any

Net weight

899 g

## Environmental conditions

Ambient temperature	-25 ... +45 °C
• during storage	-40 ... +75 °C

**Certificates**

Reference code	
• acc. to DIN EN 61346-2	F
• acc. to DIN EN 81346-2	F

General Product Approval	Declaration of Conformity	Test Certificates	other
--------------------------	---------------------------	-------------------	-------



[Miscellaneous](#)



[Miscellaneous](#)

[Miscellaneous](#)

**Further information**

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mfb=5SM2347-6>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/5SM2347-6>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=5SM2347-6](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=5SM2347-6)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>

