

Remote control switch Contact for 25 A Voltage 24 V DC 1 change-over contact



Model	
Product brand name	SETRON
Product designation	Remote control switch
Latching relay design	Mechanical switch
General technical data	
Electrical endurance (switching cycles)	50 000
Pulse duration / minimum	100 ms
Galvanic isolation / between magnet coil and contact	Yes
Switching voltage / of the contacts / at AC / minimum	10 V
Switching current / at AC / per contact / minimum	100 mA
Power loss [V·A] / of magnet coil / with pulse / rated value	9 V·A
Voltage	
Continuous voltage fuse version	Yes
Surge voltage resistance / rated value	3 kV
Supply voltage	400 V
Supply voltage	
Type of voltage	AC

Supply voltage	230 ... 400 V
Protection class	
Protection class IP	IP20
Switching capacity	
Switching capacity apparent power	
• for fluorescent lamp load with DUO circuit	2 436 V·A
• for fluorescent lamp load with parallel compensation	986 V·A
• for uncompensated fluorescent lamp load	1 624 V·A
Switching capacity current	
• at cos phi 0.6	25 A
• Rated value	25 A
Switching capacity active power / with filament lamp load	5 500 W
Dissipation	
Power loss [W]	
• at 16 A / per contact / rated value	2 W
• of magnet coil / with pulse / rated value	9 W
Control current	
Type of voltage	
• of control voltage_1	DC
Control voltage	
• _1 / initial value	207 V
• _1 / Full-scale value	253 V
• _1 / setpoint	24 V
Product details	
Product component / Switch position indicator	Yes
Product function	
Product function / direct operation	Yes
Number	
Number of terminals	3
Number of NC contacts	0
Number of NO contacts	0
Number of CO contacts	1
Connections	
Connectable conductor cross-section	
• for flexible conductor / with core end processing	1 ... 10 mm ²
• for rigid conductor	1 ... 10 mm ²
Mechanical Design	

Height	90 mm
Width	17.5 mm
Width of opening / of the contacts	3 mm
Depth	73 mm
Mounting height	90 mm
Installation depth	73 mm
Number of width units	1
Mounting type	DIN rail
Mounting position	Horizontal and vertical
Net weight	174 g

Environmental conditions

Ambient temperature	-25 ... +55 °C
---------------------	----------------

Certificates

Reference code

- acc. to DIN EN 61346-2 K
- acc. to DIN EN 81346-2 K

Declaration of Conformity

Test Certificates

[Miscellaneous](#)



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5TT4437-5>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5TT4437-5>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TT4437-5

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





