



MAINS CHOKE F.FU; PHASES:3; UN1(V):690;
 ITHMAX 1(A) / F1(HZ):91 /50; I LN (A):81,9; UK(%):2;
 LN(MH):0,279; TA/ISOKL:40 /H; IP00; TYPE OF
 TERMINALS:FLAT-TYPE TERMINAL; EN 61558-2-20
 >UL/CSA-RECOGNIZED< >CHOKE<

Figure similar

General technical data:		
Product designation		Netzdrossel f. FU
Phase number		3
Type of voltage		AC
Operating voltage rated value	V	690
Operating frequency rated value	Hz	50
Current		
• at AC		
— rated value	A	81.9
— maximum	A	91
Inductivity rated value	H	0.00028
Relative inductive drop in voltage on the measurement level current, voltage and frequency	%	2
Power loss [W] of the coil	W	125
Power loss [W] of the iron core	W	28
Mechanical data:		
Type of electrical connection for main current circuit		flat connector

Width	m	0.225
Height	m	0.21
Depth	m	0.147

Ambient conditions:

Thermal class acc. to IEC 60085		H
Ambient temperature rated value	°C	40
Protection class IP		IP00

Certificates/ approvals:

General Product Approval	other
--------------------------	-------



[Confirmation](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4EU2452-3UA00-0AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4EU2452-3UA00-0AA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4EU2452-3UA00-0AA0&lang=en

last modified:

09/13/2019