

auxiliary current switch, Central half module



Model	
Product brand name	SENTRON
Product designation	Remote control switch
Latching relay design	mechanical for central control
General technical data	
Pulse duration / minimum	50 ms
Galvanic isolation / between magnet coil and contact	Yes
Switching voltage / of the contacts / at AC / minimum	10 V
Switching current / at AC / per contact / minimum	100 mA
Supply voltage	
Type of voltage	AC
Protection class	
Protection class IP	IP20
Switching capacity	
Switching capacity current	16 A
• at cos phi 0.6	
Product function	

Product function / direct operation	Yes
-------------------------------------	-----

### Number

Number of NC contacts	0
Number of NO contacts	0
Number of CO contacts	0

### Mechanical Design

Height	90 mm
Width	9 mm
Width of opening / of the contacts	1.2 mm
Depth	73 mm
Mounting height	90 mm
Installation depth	73 mm
Number of width units	0.5
Mounting type	DIN rail
Mounting position	Horizontal and vertical
Net weight	45 g

### Environmental conditions

Ambient temperature	-25 ... +70 °C
---------------------	----------------

### Certificates

Reference code	
<ul style="list-style-type: none"> <li>• acc. to DIN EN 61346-2</li> <li>• acc. to DIN EN 81346-2</li> </ul>	<p>K</p> <p>K</p>

### Declaration of Conformity



### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5TT4931>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/5TT4931>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5TT4931](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TT4931)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



