

Miniature circuit breaker 400 V 15kA, 3-pole, C, 20 A, D=70 mm



Model	
Product brand name	SENTRON
Product designation	Miniature circuit breaker
General technical data	
Number of poles	3
Number of poles / Note	3P
Tripping characteristic class	C
circuit-breaker / Design	5SY7
Mechanical service life (switching cycles) / typical	10 000
Overtoltage category	III
Voltage	
Insulation voltage	
<ul style="list-style-type: none"> <li>with single-phase operation / at AC / rated value</li> </ul>	440 V
<ul style="list-style-type: none"> <li>with multi-phase operation / at AC / rated value</li> </ul>	440 V
Supply voltage / with single-phase operation / at AC / rated value	230 V
Supply voltage	

Type of voltage	AC
Current / at AC / rated value	20 A
Supply voltage	
• at AC / rated value	400 V
Operating voltage	
• at DC / rated value / maximum	72 V
Supply voltage frequency	
• rated value	50/60 Hz

<b>Protection class</b>	
Protection class IP	IP20, with connected conductors

<b>Switching capacity</b>	
Switching capacity current	
• at DC / acc. to IEC 60947-2 / rated value	15 kA
• acc. to EN 60898 / rated value	15 kA
• acc. to IEC 60947-2 / rated value	25 kA
Energy limiting class	3

<b>Dissipation</b>	
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	1.7 W
Suitability for operation	Mechanical engineering / industry

<b>Product details</b>	
Product function / neutral conductor switching	No
Product feature / Touch protection	Yes
Product component	
• combined terminal top	Yes
• combined terminal bottom	Yes
Product feature	
• Properties for main switches in accordance with EN 60204-1	Yes
• halogen-free	Yes
• sealable	Yes
• silicon-free	Yes
Product extension / can be installed / supplementary devices	Yes

<b>Short circuit</b>	
Breaking capacity short-circuit current (I <sub>cn</sub> )	
• at AC / acc. to UL 1077 and CSA C22.2 No.235	5 kA

<b>Connections</b>	
• Connectable conductor cross-section	
— solid	0.75 ... 35 mm <sup>2</sup>

— stranded	0.75 ... 35 mm <sup>2</sup>
• Connectable conductor cross-section / finely stranded / with core end processing	0.75 ... 25 mm <sup>2</sup>
AWG number / as coded connectable conductor cross section	18 ... 4
Tightening torque [lbf·in] / with screw-type terminals	22 ... 31 lbf·in
Tightening torque / with screw-type terminals	2.5 ... 3.5 N·m
Position / of power supply cord	Any

### Mechanical Design

Height	90 mm
Width	54 mm
Depth	76 mm
Installation depth	70 mm
Number of width units	3
Mounting type	Quick assembly system
Mounting position	any
Net weight	472 g

### Environmental conditions

Influence of the surrounding temperature	max. 95% to 55°C, max. 55% to 70°C, max. 35% to 75°C
Ambient temperature	-40 ... +70 °C
• during storage	-40 ... +75 °C

### Certificates

Reference code	
• acc. to DIN EN 61346-2	F
• acc. to DIN EN 81346-2	F

## General Product Approval



CCC



IMQ



UR



VDE



RCM

[Miscellaneous](#)

Declaration of  
Conformity

Shipping Approval

Railway



EG-Konf.



ABS



BUREAU  
VERITAS



LRS



RINA

[Confirmation](#)

## Railway

[Vibration and Shock](#)

## Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SY7320-7>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/5SY7320-7>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SY7320-7](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SY7320-7)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>





