

Miniature circuit breaker 400 V 6kA, 3-pole, C, 1.6 A, D=70 mm



Model

Product brand name	SENTRON
Product designation	Miniature circuit breaker

General technical data

Number of poles	3
Number of poles / Note	3P
Tripping characteristic class	C
circuit-breaker / Design	5SY6
Mechanical service life (switching cycles) / typical	10 000
Overvoltage category	III

Voltage

Insulation voltage	
<ul style="list-style-type: none"> • with single-phase operation / at AC / rated value 	440 V
<ul style="list-style-type: none"> • with multi-phase operation / at AC / rated value 	440 V
Supply voltage / with single-phase operation / at AC / rated value	230 V

Supply voltage

Type of voltage	AC
Current / at AC / rated value	1.6 A
Supply voltage	
• at AC / rated value	400 V
Operating voltage	
• at DC / rated value / maximum	72 V
Supply voltage frequency	
• rated value	50/60 Hz

Protection class	
Protection class IP	IP20, with connected conductors

Switching capacity	
Switching capacity current	
• at DC / acc. to IEC 60947-2 / rated value	15 kA
• acc. to EN 60898 / rated value	6 kA
• acc. to IEC 60947-2 / rated value	30 kA
Energy limiting class	3

Dissipation	
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	1.2 W

Current	
Tripping residual / rated value / derated current / at 40 Cel	1.54 A
Suitability for operation	Mechanical engineering / industry

Product details	
Product function / neutral conductor switching	No
Product feature / Touch protection	Yes
Product component	
• combined terminal top	Yes
• combined terminal bottom	Yes
Product feature	
• Properties for main switches in accordance with EN 60204-1	Yes
• halogen-free	Yes
• sealable	Yes
• silicon-free	Yes
Product extension / can be installed / supplementary devices	Yes

Short circuit	
Breaking capacity short-circuit current (I _{cn})	
• at AC / acc. to UL 1077 and CSA C22.2 No.235	5 kA

Connections

<ul style="list-style-type: none">• Connectable conductor cross-section<ul style="list-style-type: none">— solid— stranded• Connectable conductor cross-section / finely stranded / with core end processing	0.75 ... 35 mm ² 0.75 ... 35 mm ² 0.75 ... 25 mm ²
AWG number / as coded connectable conductor cross section	18 ... 4
Tightening torque [lbf·in] / with screw-type terminals	22 ... 31 lbf·in
Tightening torque / with screw-type terminals	2.5 ... 3.5 N·m
Position / of power supply cord	Any

Mechanical Design

Height	90 mm
Width	54 mm
Depth	76 mm
Installation depth	70 mm
Number of width units	3
Mounting type	Quick assembly system
Mounting position	any
Net weight	470 g

Environmental conditions

Influence of the surrounding temperature	max. 95% to 55°C, max. 55% to 70°C, max. 35% to 75°C
Ambient temperature <ul style="list-style-type: none">• during storage	-25 ... +55 °C -40 ... +75 °C

Certificates

Reference code <ul style="list-style-type: none">• acc. to DIN EN 61346-2• acc. to DIN EN 81346-2	F F
--------------------------------------------------------------------------------------------------------------------------	--------

General Product Approval



CCC



IMQ



UR



VDE

[Miscellaneous](#)



RCM

General
Product Ap-
proval

[KC](#)



EG-Konf.

Declaration of
Conformity

Test Certific-
ates

[Miscellaneous](#)

Shipping Approval



ABS



BUREAU
VERITAS



LRS

Shipping Approval



RINA

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SY6315-7>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SY6315-7>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SY6315-7

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





