

circuit breaker 3VT1 standard breaking capacity  $I_{cu}=25\text{kA}$ , 415V AC  
 4-pole, line protection trip unit TM, LI  $I_n=40\text{A}$  rated current  
 $I_R=32\text{...}40\text{A}$  overload protection  $I_I=200\text{...}400\text{A}$ , short-circuit  
 protection N conductor unprotected without auxiliary release without  
 auxiliary/alarm switch with front terminals



Model	
Product brand name	SENTRON
Product designation	3VT1_5 molded case circuit breakers
Design of the operating mechanism	toggle handle
Type of the driving mechanism / motor drive	No
Design of the overcurrent release	TM
General technical data	
Number of poles	4
Size of the circuit-breaker	3VT1
Electrical endurance (switching cycles) / typical	6 000
Usage category	A
Performance class for circuit breaker	N
Mechanical service life (switching cycles) / typical	20 000
Operating frequency / maximum	120 1/h
Voltage	
Insulation voltage / rated value	690 V
Surge voltage resistance / rated value	8 kV
Protection class	

Protection class IP	IP40
Protective function of the overcurrent release	LI
<b>Dissipation</b>	
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	1.33 W
<b>Current</b>	
Operating current / at 45 °C / rated value	38 A
Continuous current / rated value	40 A
Derating temperature / for the rated value of the continuous current	40 °C
Adjustable pick-up value current	
• of the current-dependent overload release / Full-scale value	40 A
• of instantaneous short-circuit trip unit / initial value	200 A
• of instantaneous short-circuit trip unit / Full-scale value	400 A
<b>Main circuit</b>	
Operating frequency	
• 1 / rated value	50 Hz
• 2 / rated value	60 Hz
Operating current	
• at 40 °C / rated value	40 A
• at 50 °C / rated value	38 A
<b>Auxiliary circuit</b>	
Number of CO contacts / for auxiliary contacts	0
Number of NC contacts / for auxiliary contacts	0
Number of NO contacts / for auxiliary contacts	0
<b>Suitability</b>	
Suitability for use	system protection
• Disconnecting means	Yes
<b>Adjustable parameters</b>	
Adjustable pick-up value current / of the current-dependent overload release / initial value	32 A
<b>Product details</b>	
Product component	
• Trip indicator	No
• Auxiliary switch	No
• Voltage trigger	No
• undervoltage release	No

• undervoltage release with leading contact	No
Product extension / optional / motor drive	Yes
<b>Product function</b>	
Product function	
• of thermal overload trip unit	adjustable
• Ground fault protection	No
• for neutral conductors / Short-circuit and overload proof	No
• Phase failure detection	No
• Overload protection	Yes
<b>Short circuit</b>	
Operational short-circuit current breaking capacity (Ics)	
• at 240 V / rated value	20 kA
• at 415 V / rated value	13 kA
• at 500 V / rated value	6 kA
• at 690 V / rated value	3 kA
Maximum short-circuit current breaking capacity (Icu)	
• at 240 V / rated value	40 kA
• at 415 V / rated value	25 kA
• at 500 V / rated value	12 kA
• at 690 V / rated value	6 kA
<b>Connections</b>	
Arrangement of electrical connectors / for main current circuit	front side
Type of electrical connection / for main current circuit	screw-type terminals
<b>Mechanical Design</b>	
Height	130 mm
Width	100 mm
Depth	80 mm
Mounting type	fixed mounting
Mounting position	with vertical mounting surface +/-180° rotatable, with vertical mounting surface +/- 30° tiltable to the front and back
Net weight	1.336 kg
• during operation	-40 ... +55 °C
• during storage	-40 ... +55 °C
<b>Certificates</b>	
Reference code	
• acc. to DIN EN 61346-2	Q
• acc. to DIN EN 81346-2	Q

Test Certificates	other
<a href="#">Type Test Certificates/Test Report</a>	<a href="#">Miscellaneous</a> <a href="#">Manufacturer Declaration</a>

#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VT1704-2EC45-0AA0>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3VT1704-2EC45-0AA0>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3VT1704-2EC45-0AA0](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VT1704-2EC45-0AA0)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>

-Q



