

Contactor size 2, 2-pole DC-3 and 5, 32 A Auxiliary switch 22 (2 NO + 2 NC) Alternating current operation 240 V AC 60 Hz/22 V AC 50 Hz



Product designation	Contactor
Product type designation	3TC
General technical data	
Size of contactor	2
Product extension	
• function module for communication	No
• Auxiliary switch	Yes
Insulation voltage rated value	800 V
maximum permissible voltage for safe isolation between coil and main contacts acc. to EN 60947-1	300 V
Protection class IP	IP00
• on the front	IP00
• of the terminal	IP00
Shock resistance at rectangular impulse	
• at AC	7,5g / 5 ms, 3,4g / 10 ms
Mechanical service life (switching cycles)	
• of contactor typical	10 000 000
• of the contactor with added auxiliary switch block typical	10 000 000

Reference code acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750	K
Reference code acc. to DIN EN 81346-2	Q
Reference code acc. to DIN EN 61346-2	Q

Main circuit

Number of poles	2
Number of poles for main current circuit	2
Number of NO contacts for main contacts	2
Number of NC contacts for main contacts	0
Type of voltage	AC
Operating current	
<ul style="list-style-type: none"> • with 2 current paths in series at DC-1 <ul style="list-style-type: none"> — at 24 V rated value — at 110 V rated value — at 220 V rated value — at 440 V rated value — at 600 V rated value 	32 A 32 A 32 A 32 A 32 A
Operating current with 2 current paths in series at DC-3 at DC-5	
<ul style="list-style-type: none"> • at 24 V rated value • at 110 V rated value • at 220 V rated value • at 440 V rated value • at 600 V rated value 	32 A 32 A 32 A 29 A 21 A
Operating power at DC-1	
<ul style="list-style-type: none"> • at 110 V rated value • at 220 V rated value • at 440 V rated value • at 750 V rated value 	3.5 kW 7 kW 14 kW 24 kW
Operating frequency	
<ul style="list-style-type: none"> • at DC-1 maximum • at DC-3 maximum • at DC-5 maximum 	1 500 1/s 750 1/s 750 1/s

Control circuit/ Control

Type of voltage of the control supply voltage	AC
Control supply voltage at AC	
<ul style="list-style-type: none"> • at 50 Hz rated value • at 60 Hz rated value 	220 V 240 V
Operating range factor control supply voltage rated value of magnet coil at AC	
<ul style="list-style-type: none"> • at 50 Hz • at 60 Hz 	0.8 ... 1.1 0.85 ... 1.1

Apparent pick-up power of magnet coil at AC	79 V·A
• at 50 Hz	68 V·A
• at 60 Hz	95 V·A
Inductive power factor with closing power of the coil	0.83
• at 50 Hz	0.86
• at 60 Hz	0.79
Apparent holding power of magnet coil at AC	11 V·A
• at 50 Hz	10 V·A
• at 60 Hz	12 V·A
Inductive power factor with the holding power of the coil	0.28
• at 50 Hz	0.29
• at 60 Hz	0.3
Arcing time	20 ... 30 ms

Auxiliary circuit

Number of NC contacts for auxiliary contacts	2
• instantaneous contact	2
Number of NO contacts for auxiliary contacts	2
• instantaneous contact	2
Number of CO contacts	
• for auxiliary contacts	0
Identification number and letter for switching elements	22
Operating current at AC-12 maximum	10 A
Operating current at AC-15	
• at 230 V rated value	5.6 A
• at 400 V rated value	3.6 A
• at 500 V rated value	2.5 A
Operating current at DC-12	
• at 24 V rated value	10 A
• at 48 V rated value	10 A
• at 60 V rated value	10 A
• at 110 V rated value	3.2 A
• at 125 V rated value	2.5 A
• at 220 V rated value	0.9 A
• at 600 V rated value	0.22 A
Operating current at DC-13	
• at 24 V rated value	10 A
• at 48 V rated value	5 A
• at 60 V rated value	5 A
• at 110 V rated value	1.14 A
• at 125 V rated value	0.98 A

<ul style="list-style-type: none"> • at 220 V rated value • at 600 V rated value 	<p>0.48 A</p> <p>0.07 A</p>
Contact reliability of auxiliary contacts	one incorrect switching operation of 100 million switching operations (17 V, 5 mA)

UL/CSA ratings

Contact rating of auxiliary contacts according to UL	A600 / P600
-------------------------------------------------------------	-------------

Short-circuit protection

Design of the fuse link	
<ul style="list-style-type: none"> • for short-circuit protection of the main circuit <ul style="list-style-type: none"> — with type of coordination 1 required — with type of assignment 2 required • for short-circuit protection of the auxiliary switch required 	<p>gG: 50 A (690 V, 100 kA)</p> <p>gG: 35 A (690 V, 100 kA)</p> <p>gG: 16 A (500 V, 1 kA)</p>

Installation/ mounting/ dimensions

Mounting position	+/-22,5° rotation possible on vertical mounting surface; can be tilted forward and backward by +/- 22.5° on vertical mounting surface; standing, on horizontal mounting surface
Mounting type	screw and snap-on mounting onto 35 mm standard mounting rail according to DIN EN 50022
<ul style="list-style-type: none"> • Side-by-side mounting 	Yes
Height	85 mm
Width	70 mm
Depth	104 mm
Required spacing	
<ul style="list-style-type: none"> • with side-by-side mounting <ul style="list-style-type: none"> — forwards — Backwards — upwards — downwards — at the side • for grounded parts <ul style="list-style-type: none"> — forwards — Backwards — upwards — at the side — downwards • for live parts <ul style="list-style-type: none"> — forwards — Backwards — upwards — downwards 	<p>15 mm</p> <p>0 mm</p> <p>10 mm</p> <p>10 mm</p> <p>10 mm</p> <p>30 mm</p> <p>0 mm</p> <p>10 mm</p> <p>10 mm</p> <p>10 mm</p> <p>30 mm</p> <p>0 mm</p> <p>10 mm</p> <p>10 mm</p>

— at the side

10 mm

Connections/ Terminals


Type of electrical connection <ul style="list-style-type: none">• for main current circuit• for auxiliary and control current circuit	screw-type terminals screw-type terminals screw-type terminals
Type of connectable conductor cross-sections <ul style="list-style-type: none">• for main contacts<ul style="list-style-type: none">— single or multi-stranded— finely stranded with core end processing	2x (2,5 ... 10 mm ²) 2x (1,5 ... 4 mm ²)
Type of connectable conductor cross-sections <ul style="list-style-type: none">• for auxiliary contacts<ul style="list-style-type: none">— single or multi-stranded— finely stranded with core end processing	2x (1 ... 2,5 mm ²) 2x (0,75 ... 2,5 mm ²)

Safety related data

Protection against electrical shock	finger-safe only with terminal cover
--------------------------------------------	--------------------------------------

Certificates/ approvals

General Product Approval	Functional Safety/Safety of Machinery	Declaration of Conformity
 CCC	 UL	 EG-Konf.
 CSA	 EAC	Type Examination Certificate

Declaration of Conformity	Test Certificates	Marine / Shipping	other
Miscellaneous	Special Test Certificate	Miscellaneous	Confirmation
	Type Test Certificates/Test Report	 RMRS	

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

www.siemens.com/sirius/catalogs

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3TC4417-0BP6>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3TC4417-0BP6>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3TC4417-0BP6>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)



http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3TC4417-0BP6&lang=en


Characteristic: Tripping characteristics, I²t, Let-through current

<https://support.industry.siemens.com/cs/ww/en/ps/3TC4417-0BP6/char>

Further characteristics (e.g. electrical endurance, switching frequency)

<http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3TC4417-0BP6&objecttype=14&gridview=view1>





last modified:

09/12/2019