

LV HRC fuse element, NH2, In: 400 A, gG, Un AC: 400 V, Combined indicator, insulated Grip lugs



Model	
Product brand name	SETRON
Product designation	LV HRC fuse link
Design of the product	With blade contacts
Design of an identification indicator	Combination alarms
Design of the switching contact	Non-corroding, silver-plated
Design of the fuse link	LV HRC fuse link
General technical data	
Size of fuse system / acc. to DIN EN 60269-1	NH2
Operating class of the fuse link	gG
circuit-breaker / Design	3NA6
Type of voltage	AC
Current / at AC / rated value	400 A
Supply voltage	
• at AC / rated value	400 V
Protection class	
Protection class IP	IP20, with connected conductors
Switching capacity	

Switching capacity current	
<ul style="list-style-type: none"> <li>• acc. to IEC 60947-2 / rated value</li> </ul>	120 kA

### Dissipation

Power loss [W]	29 W
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	29 W

### Current

Tripping residual / rated value / derated current / at 40 Cel	380 A
---	-------

### Mechanical Design

Width	
<ul style="list-style-type: none"> <li>• of the enclosure</li> </ul>	57.8 mm
Mounting position	Any, preferably vertical
Net weight	655 g

### Environmental conditions

Ambient temperature	-5 ... +40 °C
<ul style="list-style-type: none"> <li>• during storage</li> </ul>	Air humidity 90% at 20 °C
Environmental category	-20 to +50 at 95% relative humidity

### Certificates

Reference code	
<ul style="list-style-type: none"> <li>• acc. to DIN EN 61346-2</li> </ul>	F
<ul style="list-style-type: none"> <li>• acc. to DIN EN 81346-2</li> </ul>	F

General Product Approval	Test Certificates	Shipping Approval	other
--------------------------	-------------------	-------------------	-------



[Special Test Certificate](#)

[Miscellaneous](#)



[Miscellaneous](#)

GL

### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NA6260-4>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3NA6260-4>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**



[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NA6260-4](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NA6260-4)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



1

-F1



2