

SETRON, Fuse switch disconnecter 3NP5, 3-pole, NH1, 250 A, for assembly and installation on mounting plate, with High-speed closing, Clamp terminal



Figure similar

Model	
Product brand name	SETRON
Product designation	3NP5 fuse switch disconnecter
Design type	For assembly and installation, with high-speed closing
Design of the operating mechanism	Cover handle
Design of the load switch / Strip form	No
General technical data	
Number of poles	3
Size of disconnecting link	NH0, NH1
Size of fuse link	NH0, NH1
Continuous current / at 35 °C / rated value	250 A
power factor cos phi / in utilization category	
• AC-21 B / at 400 V	0.95
• AC-21 B / at 500 V	0.95
• AC-22 B / at 400 V	0.65
• AC-22 B / at 500 V	0.65
circuit-breaker / Design	3NP526

Mounting type	Fixed mounting
Fuse system	LV HRC fuse
Voltage	
Insulation voltage / rated value	690 V
Surge voltage resistance / rated value	6 kV
Type of voltage	AC/DC
Operating voltage	
<ul style="list-style-type: none"> • at AC / rated value / maximum • at AC / at 50/60 Hz / rated value • at DC / rated value 	<p>690 V</p> <p>690 V</p> <p>440 V</p>
Protection class	
Protection class IP / on the front	IP00
Dissipation	
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	2.66 W
Current	
Current / rated value	250 A
Continuous current	
<ul style="list-style-type: none"> • rated value • at 40 °C / rated value • at 45 °C / rated value • at 50 °C / rated value • at 55 °C / rated value • at 60 °C / rated value • at 65 °C / rated value • at 70 °C / rated value 	<p>250 A</p> <p>250 A</p> <p>250 A</p> <p>240 A</p> <p>228 A</p> <p>218 A</p> <p>205 A</p> <p>190 A</p>
Let-through current / I _{2 t} / maximum permissible / in utilization category	
<ul style="list-style-type: none"> • AC-21 B / at 400 V • AC-21 B / at 500 V • AC-22 B / at 400 V • AC-22 B / at 500 V 	<p>800 000 A²·s</p> <p>800 000 A²·s</p> <p>800 000 A²·s</p> <p>800 000 A²·s</p>
Let-through current / I _c / maximum permissible / in utilization category	
<ul style="list-style-type: none"> • AC-21 B / at 400 V • AC-21 B / at 500 V • AC-22 B / at 400 V • AC-22 B / at 500 V 	<p>25 kA</p> <p>25 kA</p> <p>25 kA</p> <p>25 kA</p>
Main circuit	
Rated current I _e / maximum / in utilization category	
<ul style="list-style-type: none"> • AC-21 B / at 400 V 	250 A

- AC-21 B / at 500 V 250 A
- AC-22 B / at 400 V 250 A
- AC-22 B / at 500 V 250 A

Suitability

Suitability for use	system protection
• Main switch	No
• switch disconnecter	Yes
• EMERGENCY OFF switch	No
• safety switch	Yes

Product function

Product function / fuse monitoring	No
------------------------------------	----

Short circuit

Maximum short-circuit current breaking capacity (Icu) / at 400 V / rated value	2.5 kA
Conditional rated short-circuit current / in utilization category	
• AC-21 B / at 400 V	50 kA
• AC-21 B / at 500 V	50 kA
• AC-22 B / at 400 V	50 kA
• AC-22 B / at 500 V	50 kA

Connections

Type of electrical connection	35 - 120 mm ²
• for main current circuit	terminal clamp

Mechanical Design

Height	300 mm
Width	207 mm
Depth	176 mm
Number of width units	1
Mounting type	Mounting plate
Mounting type	
• floor mounting	Yes
• front mounting	No
• rail mounting	No
Net weight	5 649 g

Environmental conditions



Installation altitude / at height above sea level / maximum	2 000 m
• during operation	-25 ... +55 °C
• during storage	-50 ... +80 °C

Certificates

Reference code

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

Q
Q

General Product Approval	Declaration of Conformity	Test Certificates	other
 CCC	 EG-Konf.	Special Test Certificate	Miscellaneous Confirmation

[Miscellaneous](#)

[Special Test Certificate](#)

[Miscellaneous](#)

[Confirmation](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NP5260-0CB00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NP5260-0CB00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NP5260-0CB00

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

