



TRANSFORMER SITAS; PHASES:1;
 PN/PN(S6)(KVA):8 /28,5; UPRI(V):400+/-5%;
 USEC(V):230; ISEC(A):34,8; F(HZ):50...60; VECTOR
 GR./SHIELD WNG.:II0 /0; TA/ISOKL:55 /H; IP00; TYPE
 OF TERMINALS:SCREW CONNECTION;
 INSTALLATION:SCREW; EN 61558-2-1, -2-2, -2-4
 >UL/CSA-RECOGNIZED< >CONTROL CIRCUIT
 TRANSFORMER< >ISOLATION TRANSFORMER<

Figure similar

General technical data:		
Product designation		transformer SITAS
Product brand name		SIDAC
Operating apparent output rated value	V·A	8 000
Efficiency		0.95
Connection method for transformers		II0
Certificate of suitability		CE / cRUus
Product function		
• Temperature monitoring		No
• Insulation monitoring		No
• Short-circuit and overload proof		No
Number of shielding windings		0
Short-term vector power	V·A	31 100
Relative short-circuit voltage	%	4.13
Inputs:		
Phase number of the inputs		1
Input voltage		

• _1 rated value	V	420
• _2 rated value	V	400
• _3 rated value	V	380
Electrical input frequency		
• minimum	Hz	50
• maximum	Hz	60

Outputs:		
Phase number of the outputs		1
Output voltage		
• _1 rated value	V	230
Electrical output frequency		
• maximum	Hz	60
• minimum	Hz	50

Ambient conditions:		
Thermal class acc. to IEC 60085		H
Ambient temperature rated value	°C	55
Protection class IP		IP00

Mechanical data:		
Type of electrical connection		
• at output for main current circuit		screw-type terminals
• at input for main current circuit		screw-type terminals
Mounting type		screws
Construction form of the iron core		UI 210/70
Width	m	0.226
Height	m	0.37
Depth	m	0.174

Certificates/ approvals:			
General Product Approval	Declaration of Conformity	Shipping Approval	other
	 EG-Konf.	 PRS	Confirmation

Further information
Information- and Downloadcenter (Catalogs, Brochures,...) http://www.siemens.com/industrial-controls/catalogs
Industry Mall (Online ordering system) http://www.siemens.com/industrymall
Cax online generator http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=4AT3912-5AT10-0FA0

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4AT3912-5AT10-0FA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AT3912-5AT10-0FA0&lang=en

last modified:

01/20/2019